



Eveready Battery Company, Inc.


533 Maryville University Drive
 St. Louis, MO 63141
 Telephone 1-800-383-7323
 Internet: www.energizer.com

Engineering Data

**Zinc Chloride 1.5V
 Super Heavy Duty**
 No Added Mercury or Cadmium

EVEREADY NO. 1235

Dimensions (mm)



Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)

Designation: ANSI-14D, IEC-R14

Battery Voltage: 1.5 Volts

Average Weight: 45 grams (1.6 oz.)

Volume: 25 cubic centimeters (1.5 cubic inch)


Average Service capacity (to 0.8 Volts): 3,000 mAh
 (Rated Capacity at 25 mA continuous drain)

Cell: One No. 35 (size "C")


Jacket: Metal

Millimeters	Inches
0.10	0.004
0.70	0.028
2.30	0.091
4.30	0.169
25.00	0.984
26.20	1.031
45.60	1.795
46.50	1.831
48.60	1.913
49.80	1.961





CONSTANT RESISTANCE PERFORMANCE
 Typical Service



CONSTANT CURRENT PERFORMANCE
 Typical Service



Typical Applications



Important Notice

This data sheet contains information specific to batteries manufactured at time of its publication. Please contact your Energizer representative for most current information. Contents herein do not constitute a warranty.