



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Body Type:	Aluminium
Dimmable:	No
Rated Load:	Max 35W
Dimension:	1170x50mm

BOLLARD LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7554 -

[View more details](#)

**CLASSIC &
DURABLE
DESIGN**

- ALUMINIUM BODY
- EASY TO INSTALL
- LOW MAINTENANCE



FEATURES

- Traditional garden lamps designed to meet modern day requirements
- Strong and sturdy Aluminium body
- Offering IP44 Ingress protection
- Compatible with GU10 holder type (Fitting only - light not included)
- Suitable for gardens, patio, pathways etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs):	1.646
Unit CBM:	0.012636
Dimension:	1170x50mm

MASTER BOX PACKAGING

Box Qty:	6
Qty Per Pallet:	108
Length (Box) mm:	120
Width (Box) mm:	130
Height (Box) mm:	810

LISTING DETAILS

Commodity Code:	9405109890
EanCode:	3800157633581