
WC Series Crystal



- 32.768KHZ
- **Standard Cylindrical Holders**
- **RoHS Compliant**



Series	WC155	WC26	WC38
Frequency Range	32.768KHZ	32.768KHZ	32.768KHZ
Frequency Tolerance	See Part Number Guide	See Part Number Guide	See Part Number Guide
Frequency Stability	$034(\pm .006)$ ppm/°C ² (T-To) ²	$034(\pm .006)$ ppm/°C ² (T-To) ²	$034(\pm.006)$ ppm/°C ² (T-To) ²
Turnover Temperature (To)	+25°C ±5°C	+25°C ±5°C	+25°C ±5°C
Operating Temp. Range	-20°C to +70°C	-20°C to +70°C	-20°C to +70°C
Storage Temp. Range	-40°C to +85°C	-40°C to +85°C	-40°C to +85°C
Aging	±3ppm / 1 st year max	±3ppm / 1 st year max	±3ppm / 1 st year max
Shunt Capacitance	1.00pF typical	1.35pF typical	1.60pF typical
Equivalent Series Resistance	40K Ohms max	35K Ohms max	35K Ohms max
Load Capacitance	6pF, 8pF, or12.5pF	6pF, 8pF, or12.5pF	6pF, 8pF, or12.5pF
Drive Level	1uWatt max	1uWatt max	1uWatt max
Motional Capacitance	2.5fF typical	3.0fF typical	3.5fF typical
Capacitance Ratio	400 typical	450 typical	460 typical
Quality Factor	80K typical	70K typical	90K typical

Mechanical Details






NOTES
1. CAN PLATING = Ni
2. LEADING PLATING = Sn95% - 98%,
Cu 2% -5%

Series	A	В	C	ם
WC155	1.5 [.059]	5.1 [.201]	4.3 [.169]	0.2 [.008]

Series	A	B	C	ם	E
WC155	1.5 [.059]	5.1 [.201]	4.3 [.169]	0.2 [.008]	0.45 [.018]
WC26	2.1 [.083]	6.2 [.244]	7.0 [.276]	0.26 [.010]	0.7 [.028]
WC38	3.1 [.122]	8.2 [.323]	10.0 [.394]	.35 [.014]	1.1 [.043]

Part Number Guide



Please consult with MMD sales department for any other parameters or options.



MMD Monitor/Quartztek

30400 Esperanza, Rancho Santa Margarita, CA, 92688 Phone: (949) 709-5075, Fax: (949) 709-3536, <u>www.mmdcomp.com</u> Sales@mmdcomp.com

Revision:	WC082812J