



Creating Safe Work Solutions During COVID-19

Q5XKLA5000-Q8

► Q5X SERIES HIGH POWER, MID RANGE PHOTOELECTRIC SENSOR



Q5X Series: Laser Adjustable Field
 Range: 50 to 5000 mm; Input 10-30 V dc
 Output: 1 PNP/NPN with IO-Link; 1 PNP/NPN Multi-Function I/O
 Connection: Euro M12 4-pin Rotatable Connector
 Part Number: 807731

CERTIFICATIONS



SPECIFICATIONS











Sensing Mode (General)	Proximity
Sensing Mode (Detailed)	Background/Foreground Suppression
Housing Style	Rectangular
Primary Housing Material	ABS
Laser Classification	Class 2
Input/Output	Discrete
Indicator	Display; LED(s)
Analog Resolution/Discrete Repeatability	TBD

Max Sensing Distance (mm)	5000
Minimum Sensing Distance (mm)	50
Sensing Beam	Visible Red Laser
Power Supply	10-30 V dc
Delay at Power-up (ms)	2500
Sensing Beam Wavelength (nm)	650
Adjustments	Push Button; Remote Teach
Temperature Effect (mm/°C)	< +/- 0.5 mm/°C < 3000 mm, < +/- 0.75 mm/°C at < 5000 mm
Connection	Integral QD
QD Type/Cable Length	M12 (Euro) requires mating cordset
Number of Pins	4
Vibration	MIL-STD-202G req. Method 201A (vibration:10 to 60Hz max., double amplitude 0.06", max acc. 10G).
Mechanical Shock	MIL-STD-202G, Meth. 213B, Cond. I (100G 6x along X, Y & Z axes, 18 total shocks) w/ sensor operating
Output Saturation Voltage NPN Outputs	< 2.5 V @ 50 mA
Output Saturation Voltage PNP Outputs	< 2.5 V @ 50 mA
Max Discrete (Switched) Output (mA)	50
Discrete (Switched) Outputs	2 NPN/PNP Configurable
Output Protection	Protected against continuous overload and short circuit
IP Rating	IP67
Storage Temperature (°C)	-25 to 70
Max Operating Temperature (°C)	50
Min Operating Temperature (°C)	-10
Max Op. Relative Humidity Non-Condensing (%)	95 at 50°C
Window Material	PMMA








Warm-up Time (minutes)	10
Minimum Response Time (ms)	2
Spot Size (@ Reference Distance)	TBD
Minimum Window Size (mm)	1
Discrete Output Hysteresis (mm)	Automatically adjusted
Laser Control	Yes
Max Ambient Light (Lux)	up to 5000 lux at 1000 mm and up to 2000 lux at 2000 mm
Power/Current Consumption (exclusive of load)	< 1 W
Supply Protection Circuitry	Protected against reverse polarity and transient overvoltages
Feature: Remote Teach	Yes
Feature: Clear Object Detection	Yes
Feature: Timing (Hold/Delay)	Yes
Feature: Chemical Resistant	No
Feature: Pump-in/ Pump-out	Yes
Common Ethernet Protocol	No
IO Link	Yes
PROFINET	No
RS-232	No
RS-422	No
RS-485	No
SSI	No
Wireless	No
1-wire Serial Interface	No
Profibus	No

COMPATIBLE PRODUCTS




BRACKET

	<p>SMB30A</p> <p>Bracket: Right Angle Mounting
Material: 12 Gauge Stainless Steel
Curved mounting slot for versatility/orientation
Clearance for M6 (1/4 in.) hardware</p>
	<p>SMBAMSQ5XIPP</p> <p>Bracket: Straight or Flat Bracket with
AMS Mounting
Including Side Impact and Glass Window</p>
	<p>SMBAMSQ5XIPRA</p> <p>Bracket: Right Angle or L Bracket with
AMS Mounting
Including Side Impact and Glass Window</p>
	<p>SMBAMSQ5XP</p> <p>Bracket: Straight or Flat Bracket with
AMS Mounting Only
No Industrial Protection Components</p>
	<p>SMBAMSQ5XRA</p> <p>Bracket: Right Angle or L Bracket with
AMS Mounting Alone
No Industrial Protection Components</p>
	<p>SMBQ5XDT</p> <p>Bracket: Dove Tail Set
Aluminum Extrusions and Associated Bolts</p>
	<p>SMBQ5XFAM10</p> <p>Bracket: Kit for 12 mm (1/2 in) Rod Bracket System
for: Q5X, QM42, PD45, PD49, QC50
Includes 3/8-16 X 2 in.
Socket Head Cap Screw (SHCS)</p>
	<p>SMBQ5XFAM12</p> <p>Bracket: Kit for 10mm (3/8in) Rod Bracket Systems
for:Q5X, QM42, PD45, PD49, QC50
Includes M10-1.5x100mm
Socket Head Cap Screw(SHCS)</p>
	<p>SMBQ5XFAM12</p> <p>Bracket: Kit for 12 mm (1/2 in) Rod Bracket Systems
for: Q5X, QM42, PD45, PD49, QC50
No Socket Head Cap Screw (SHCS) included</p>
	<p>SMBQ5XM4F</p> <p>Bracket: M4 Fixing Plates
M4 Socket Head Cap Screw
Qty = 2 of Each Part</p>

DOUBLE-ENDED CORDSETS



	<p>MQDC-4501SS</p> <p>Euro-Style QD to Euro-Style QD
5-pin Euro Straight Male; 4-pin Euro Straight Female
0.3 m (1.0 ft) in Length
Nickel-Plated Brass Coupling Nuts; PVC Jacketed Cable
4x22AWG Conductors; No Shield</p>
	<p>MQDC-4506SS</p> <p>Euro-style QD to Euro-style QD
5 Pin Euro Straight Male; 4 Pin Euro Straight Female
1.83 m (6.0 ft) in Length
Nickel-Plated Brass Coupling Nuts; PVC Jacketed Cable; 4x22AWG Conductors; No Shield</p>
	<p>MQDEC-406SS</p> <p>Euro-style Quick Disconnect Cable
4-pin Straight Connector
2 m (6.5 ft) Length
Double Ended With 1 Female & 1 Male Connector</p>
	<p>MQDEC-406SS-PUR</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 2 m Length
Chrome plated brass coupling nut</p>
	<p>MQDEC-412SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 3.7 m Length
Chrome plated brass coupling nut</p>
	<p>MQDEC-415SS-PUR</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 5 m Length
Chrome plated brass coupling nut</p>
	<p>MQDEC-430SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 9.1 m Length
Chrome plated brass coupling nut</p>

SINGLE-ENDED CORDSETS


	<p>MQDC-406</p> <p>Euro-style Quick Disconnect Cable
4-Pin Straight Connector
2 m (6.5 ft) in Length
Nickel-plated Brass Coupling Nut</p>
	<p>MQDC-406RA</p> <p>Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
2 m (6.5 ft) in Length
Nickel-plated brass coupling nut</p>
	<p>MQDC-415</p> <p>Euro-style Quick Disconnect Cable
4-Pin Straight Connector
5 m (15 ft) in Length
Nickel-plated Brass Coupling Nut.</p>

	<p>MQDC-415RA</p> <p>Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
5 m (15 ft) in Length
Nickel-plated brass coupling nut</p>
	<p>MQDC-430</p> <p>Euro-style Quick Disconnect Cable
4-Pin Straight Connector
9 m (30 ft) in Length
Nickel-plated Brass Coupling Nut</p>
	<p>MQDC-430RA</p> <p>Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
9 m (30 ft) in Length
Nickel-plated brass coupling nut</p>
	<p>MQDC-450</p> <p>Euro-Style Quick Disconnect Cable
4-Pin Straight Connector
15 m (50 ft) in Length
Nickel-plated Brass Coupling Nut</p>
	<p>MQDC-450RA</p> <p>Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
15 m (50 ft) in Length
Nickel-plated brass coupling nut</p>

REPLACEMENT WINDOW

	<p>RWSMBQ5XIP-1</p> <p>Accessory: One Piece of Glass Replacement
for SMBQ5XIP</p>
	<p>RWSMBQ5XIP-5</p> <p>Accessory: Five Pieces of Glass Replacement
for SMBQ5XIP</p>

REMOTE SENSOR DISPLAY

	<p>RSD1QP</p> <p>RSD Series Remote Display
Single Sensor Support
Output: Depends on Sensor
Euro 5-pin 150 mm (6 in) PVC Pigtail</p>
---	---



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America