

**Basic 160-6 W OF (601501000) Compressor Basic
Cardboard box**

Order no. 601501000
EAN 4061792174061



Product may differ from Image



- Compact 6 litre compressor with powerful motor for universal use
- Ideal for stapling, nailing, blowing out, filling of tyres as well as for working with cartridge guns, grease guns and riveting guns
- Easy carrying and space-saving storage thanks to folding handle and small dimensions
- Oil-free piston compressor: simple transportation and reduced service requirements
- Instrument panel with easy to read manometers for tank- and working pressure
- Operating pressure can be regulated according to application by means of a pressure reducer and manometer
- Overload protection: protects the motor from overheating
- Rubberised feet for optimum stability also during transport
- Comfortable condensate outlet via ball valve with wing grip
- 10 year tank warranty against rust

Technical data**Characteristics**

Suction rate	160 l/min
Filling capacity	65 l/min
Effective delivery volume (at 80% max. pressure)	55 l/min
Maximum pressure	8 bar
Rated input power	0.9 kW
Maximum speed	3500 rpm
Tank capacity	6 l
Sound pressure level (LpA)	82 dB(A)
Sound power level (LwA)	94 dB(A)
Dimensions	340 x 300 x 290 mm
Weight	8.4 kg
Cable length	1.5 m

Noise emission

Sound pressure level	82 dB(A)
Sound power level (LwA)	94 dB(A)

Scope of delivery

Universal quick-action coupling