



Data sheet | Item number: 221-510/000-006

Mounting carrier; 221 Series - 6 mm²; for DIN-35 rail mounting/screw mounting; blue

www.wago.com/221-510/000-006



RoHS Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:

Data

Physical data

Width	19.3 mm / 0.76 inch
Height from upper-edge of DIN-rail	28.3 mm / 1.114 inch
Depth	94.2 mm / 3.709 inch

Mechanical data

Mounting type	DIN-35 rail Screw mount
Suitable	für 2-, 3-, 5-Leiter-Verbindungsklemmen (6 mm ²) der Serie 221

Material Data

Color	blue
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Weight	11.9 g

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

Commercial data

Packaging type	BOX
Country of origin	CN
GTIN	4055143833554
Customs tariff number	39269097900

Counterpart

Compatible products

Mounting adapter



Item no.: 222-505

Strain relief plate; for mounting carrier; 221 or 222 Series, can be snapped

www.wago.com/222-505



Item no.: 222-510

Angled DIN-rail adapter; in combination with mounting carrier; 221-500 or 222-500; for DIN-35 rail mounting; gray

www.wago.com/222-510

Marking accessories



Item no.: 210-833

Marking strips; on reel; 6 mm wide; plain; Self-adhesive; white

www.wago.com/210-833

Downloads

Documentation

Additional Information

Technical explanations	03-Apr-2019	pdf 2.2 MB	Download
------------------------	-------------	---------------	----------

CAD/CAE-Data

CAD data

2D/3D Models 221-510/000-006	URL	Download
------------------------------	-----	----------


CAE data

ZUKEN Portal 221-510/000-006	URL	Download
------------------------------	-----	----------


Subject to changes. Please also observe the further product documentation!

Installation Notes

Conductor termination




CAGE CLAMP® connection:




Removing a conductor.


Conductor termination with connectors fitted in a mounting carrier



Inserting a connector into the mounting carrier.




Inserting a connector into the mounting carrier.




Removing a connector from the mounting carrier.


Subject to changes. Please also observe the further product documentation!




Securing a strain relief plate (222-505) to the mounting carrier.




Snapping the angled DIN-rail adapter (222-510) onto the mounting carrier.



Horizontal mounting on DIN-35 rail using an angled DIN-rail adapter.



Horizontal mounting on DIN-35 rail using an angled DIN-rail adapter.




Horizontal screw mounting with strain relief plate on a flat surface




Vertical mounting with strain relief plate on DIN-35 rail.


Subject to changes. Please also observe the further product documentation!



Strain relief via cable ties on the mounting carrier (transverse to the connectors' wiring direction) – clamping units labeled via marking strips (210-334).




Vertical screw mounting with strain relief plate on a flat surface.



Mounting carrier on a DIN-35 rail

Testing



Testing connectors via test slots on top of the carrier.

Subject to changes. Please also observe the further product documentation!