ΗΙΟΚΙ

AC FLEXIBLE CURRENT SENSOR CT9667

Introducing 2 new variations with a thinner cable!




Easy to loop around, even in confined spaces



Use with a power quality analyzer or power meter

CE

Thinner cable type is easy to use in confined spaces and with complex wiring



- D - - ' - - -

Basic specifications (Accuracy guaranteed for 1 year, Post-adjustment accuracy guaranteed for 1 year)					
	CT9667-01	CT9667-02			

	CT9667-01	CT9667-02	CT9667-03		
Rated input current	5000 A AC/ 500 A AC				
Max. allowable input	allowable input 10000 A continuous (45 to 66 Hz, requires derating at frequency)				
Bandwidth	dth 10 Hz to 20 kHz (±3dB)			S	
Amplitude and phase accuracy	±2 % rdg. ±0.3 % f.s. (45 to 66 Hz, at center of flexible loop) Phase: ±1 deg (45 to 66 Hz)				
Output voltage	out voltage 500 mV AC/f.s. (0.1 mV AC/A) at 5000 A range, 500 mV AC/f.s. (1 mV AC/A) at 500 A range				
Max. rated voltage to earth	1000 V AC (CAT III), 600 V AC (CAT IV)				
Core diameter	φ 100 mm (3.94 in)	φ 180 mm (7.09 in)	φ 254 mm (10.00 in)		
Output terminal		BNC		Freedow	
Operating temperature	-25 °C to +65 °C (-13 °F to 149 °F)	-25 °C to +65 °C (-13 °F to 149 °F)	-10 °C to +50 °C (14 °F to 122 °F)	E000A	
Power supply	LR6 (AA) alkaline batteries ×2, Continuous use : 7 days (rated power 35 mVA), or AC adapter 9445-02/-03 (rated power 0.2 VA), or External power supply 5 to 15 V DC (rated power 0.2 VA)				
Dust and water resistance	Flexible loo	p only: IP54	N/A	OFF	
Dimensions and mass	$ \begin{array}{l} \label{eq:starsessense} Flexible loop cable diameter: $$\phi$7.4 mm (0.29 in), Cable length: Between flexible loop and battery box: 2 m (6.56 ft), Output cable: 1 m (3.28 ft), Battery box: 35 mm (1.38 in)W \times 120.5 mm (4.74 in)H \times 34 mm (1.34 in)D, 280 g (9.9 oz) \end{array} $			Range switch	
ccessories LR6 (AA) alkaline batteries ×2, Instruction manual ×1					

Model No. (Order Code) CT9667-01 (ϕ 100 mm (0.30 in)) CT9667-02 (\$\$\phi180 mm (7.09 in)) CT9667-03 (\$\$\phi254 mm (10.00 in))

Note: These current sensors may also be used with HIOKI power quality analyzers, power meters or Memory HiCorders. CT9667 is a flexible current sensor for measuring large currents. It is not suitable for mea-





Note: Company names and product names appearing in this catalog are trademarks or registered trademarks of various companies.



suring minute current such as leakage current.



DISTRIBUTED BY

HIOKI E.E. CORPORATION

HEADQUARTERS

81 Koizumi. Ueda, Nagano 386-1192 Japan https://www.hioki.com/



regional contact information