



Main

Range of product	Acti 9
Product name	Acti 9 iQuick PRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	iQuick PRD20r
Device application	Distribution
Poles description	3P + N
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TT TN-S

Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV + GDT
[Ue] rated operational voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] nominal discharge current	Common mode: 5 kA (L/PE) Common mode: 5 kA (N/PE) Differential mode: 5 kA (L/N)
[Imax] maximum discharge current	Common mode: 20 kA L/PE Common mode: 20 kA N/PE Differential mode: 20 kA L/N
[Uc] maximum continuous operating voltage	Common mode: 264 V N/PE Common mode: 350 V L/PE Differential mode: 350 V L/N
Maximum [Up] voltage protection level	Common mode <1.5 kV type 2 L/PE Common mode <1.5 kV type 2 N/PE Differential mode <1.5 kV type 2 L/N
Disconnecter device type	Integrated circuit breaker - Icu 25 kA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Isc] short-circuit current rating	25 kA
Signalling circuit voltage	2 A/250 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	14.6
Height	94 mm
Width	131.5 mm
Depth	75.9 mm
Net weight	0.84 kg
Colour	White (RAL 9003)
Response time	<= 25 ns
Connections - terminals	Tunnel type terminal (downside) 2.5...25 mm ² Tunnel type terminal (upside) 2.5...25 mm ²
Tightening torque	2.5 N.m

Environment

Standards	EN 61643-11:2012 IEC 61643-11:2011
Product certifications	CE
Quality labels	KEMA-KEUR NF
IP degree of protection	IP40 on front face: conforming to IEC 60529 IP20 built-in: conforming to IEC 60529
IK degree of protection	IK05 conforming to IEC 62262
Relative humidity	5...90 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	874 g
Package 1 Height	9 cm
Package 1 width	10 cm
Package 1 Length	15 cm
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	10.906 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------
