



### Main

Range	Acti 9
Product name	Acti 9 iC60 RCBO
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Device short name	IC60 RCBO
Device application	Distribution
Poles description	3P
Number of protected poles	3
[In] rated current	25 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A
Breaking capacity	10000 A Icn at 220...240 V AC 50 Hz conforming to EN/IEC 61009-2-1 15 kA Icu at 220...240 V AC 50 Hz conforming to EN/IEC 60947-2
Suitability for isolation	No conforming to IEC 60947-1
Quality labels	VDE NF IMQ KEMA-KEUR

### Complementary

Device location in system	Outgoer
Network frequency	50 Hz
[Ue] rated operational voltage	220...240 V AC 50 Hz
Magnetic tripping limit	5...10 x In

Residual current tripping technology	Voltage independent
[Ics] rated service breaking capacity	7500 A 75 % x Icn at 220...240 V AC 50 Hz conforming to EN/IEC 61009-2-1 7.5 kA 50 % x Icu at 220...240 V AC 50 Hz conforming to EN/IEC 60947-2
Rated breaking and making capacity	I <sub>dm</sub> 6000 A at 220...240 V AC 50 Hz conforming to EN/IEC 61009-2-1
Limitation class	1 conforming to EN/IEC 61009-2-1
[Ui] rated insulation voltage	500 V AC 50 Hz
[Uimp] rated impulse withstand voltage	4 kV
Surge current	250 A
Contact position indicator	No
Control type	Toggle
Local signalling	ON, OFF, fault trip
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES Bottom: biconnect
9 mm pitches	6
Height	86 mm
Width	54 mm
Depth	78 mm
Net weight	334 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Tunnel type terminal top or bottom 1...35 mm <sup>2</sup> rigid Tunnel type terminal top or bottom 1...25 mm <sup>2</sup> flexible Tunnel type terminal top or bottom 1...25 mm <sup>2</sup> flexible with ferrule
Wire stripping length	12 mm for top or bottom connection
Tightening torque	2 N.m
Earth-leakage protection	Integrated

## Environment

Standards	EN/IEC 60947-2 EN/IEC 61009-2-1
IP degree of protection	IP40 (distribution enclosure) conforming to IEC 60529 IP20 conforming to IEC 60529
Overvoltage category	III conforming to IEC 60364
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61009-2-1
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...40 °C
Ambient air temperature for storage	-40...70 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	340 g
Package 1 Height	8.7 cm
Package 1 width	5.7 cm
Package 1 Length	10 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Weight	1.432 kg
Package 2 Height	10 cm
Package 2 width	11 cm

Package 2 Length	25 cm
Unit Type of Package 3	S03
Number of Units in Package 3	24
Package 3 Weight	9.192 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins