CPF0201B59RE1

TE Internal #: 2176451-8 Surface Mount Resistors, Precision Resistor, 2 Termination, 0201, Taped & Reeled, .1%, Thin Film, Resistance Range Up to $1k\Omega \Omega$, 59 Ω, .0313 W

View on TE.com >

Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Number of Terminations: 2 Surface Mount Resistor Size Code: 0201 Surface Mount Resistor Packaging Method: Taped & Reeled Surface Mount Resistor Tolerance: .1%

Features

Product Type Features



Product Type	Fixed Resistor	
Resistor Type	Precision Resistor	
Surface Mount Resistor Size Code	0201	
Element Type	Thin Film	
Configuration Features		
Number of Resistors	1	
Electrical Characteristics		
Voltage Rating	15 V	
Surface Mount Resistor Tolerance	.1%	
Resistance Range	Up to $1k\Omega$ Ω	
Surface Mount Resistor Resistance	59 Ω	
Surface Mount Resistor Power Rating	.0313 W	
Termination Features		
Number of Terminations	2	

C For support call+1 800 522 6752

CPF0201B59RE1

Surface Mount Resistors, Precision Resistor, 2 Termination, 0201, Taped & Reeled, . 1%, Thin Film, Resistance Range Up to $1k\Omega \Omega$, 59 Ω , .0313 W



Surface Mount Resistor Termination Type	Solder
Mechanical Attachment	
Mount Style	Surface Mount
Dimensions	
Surface Mount Resistor Dimensions	.58 x .29 x .23 mm
Usage Conditions	
Temperature Coefficient	±25 ppm/°C
Packaging Features	
Surface Mount Resistor Packaging Method	Taped & Reeled
Product Compliance For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2020

(209)

Does not contain REACH SVHC

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Halogen Content

Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

CPF0201B59RE1

Surface Mount Resistors, Precision Resistor, 2 Termination, 0201, Taped & Reeled, . 1%, Thin Film, Resistance Range Up to $1k\Omega \Omega$, 59 Ω , .0313 W





Customers Also Bought



3560 56R 5%	16 sys 50 hdr drra shrd sn	FFC Receptacle Housing: 1.27m
TE Model / Part #1879855-2 BMB-0.0402 30P N8	TE Model / Part #1879855-6 BMB-0 0402 300P N8	
BMB-A 0402 30R N8	BMB-A 0402 300R N8	

Documents

Product Drawings CPF 0201 59R 0.1% 25ppm 1K RL

English

Datasheets & Catalog Pages CPF-1016

English