


RRC-SCC1130

Standard battery charger

P/N: 110002



Features:

- 5.00W single bay charger
- For the standard battery RRC1130
- Optimized charging process enables longer cycle life for RRC battery
- Simple operation – Plug and Play
- External power supply for worldwide use
- Country specific AC input cables available

Applications:

Standard charging station for mobile devices used in medical, industrial and consumer markets

Specification

Input	
Voltage	5.00V nom.
Current	1.00A nom.
Power	5.00W

Output	
Voltage range	4.35VDC
Current range	1.00A
Voltage tolerance ⁽¹⁾	±1% max.
Current tolerance ⁽¹⁾	±10% max. @1.00A
Protection	Short circuit, battery over/under temperature, charge over temperature, charge timer

Environmental		
Cooling	convection cooled	
Temperature	Operating: 0°C to 40°C	Non-operating: -10°C to 70°C
Pressure & Altitude	Operating: 1060hPa to 795hPa -382m to 2000m	Non-operating: 1060hPa to 572hPa -382m to 4570m
Humidity	5% to 95% r.H., non-condensing	

General	
Indicator	Multi-color LED (green, red, orange)
Battery types	Standard battery RRC1130
Green procurement	RoHS 2011/65/EU WEEE 2012/19/EU Chinese RoHS

LED Indications	
Orange light	The inserted battery is of the correct type and is currently being charged.
Green light	The battery is charged and can be removed for use.
Red blinking	Battery detection phase
Red light	No battery inserted Battery over/under temperature error Charger over temperature error Battery over voltage error Battery charge time-out error Input voltage too low

Safety & EMC	In combination with included external AC/DC power supply	
Regulatory approvals	Europe	CE
Electromagnetic Emissions	Europe	EN55011, EN55022, level B
	USA	FCC15 class B
Electromagnetic Immunity	ESD immunity	EN/IEC61000-4-2
	Electromagnetic field immunity	EN/IEC61000-4-3
	EFT / Burst	EN/IEC61000-4-4
	Surge	EN/IEC61000-4-5
	Conducted Immunity	EN/IEC61000-4-6
	Magnetic Fields	EN/IEC61000-4-8

Specification external AC/DC power supply

Input		
Voltage range	100.00 – 240.00VAC	
Current	0.30A max.	
Stand by power	No load 0.10W @ 230.00VAC	
Output		
Voltage range	5.00VDC	
Power	5.00W max.	
Current range	1.00A	
Protection	Over voltage, short circuit	
Environmental		
Temperature	Operating: 0°C to 40°C	Non-operating -20°C to 60°C
General		
Efficiency	California's Energy Efficiency Level VI	
Line regulation	± 5%	
Ripple & Noise	200.00mV (p-p)	
Power Supply Mechanical Details		
Standard output connector	Micro USB	
Housing dimensions (LxWxH)	71.0 x 60.0 x 26.5mm for UK 60.0 x 26.0 x 40.0mm for EU 60.0 x 26.0 x 40.0mm for KR 60.3 x 41.5 x 66.3mm for AUS 60.0 x 25.2 x 40.0mm for USA/CAN/JP 68.0 x 30.0 x 35.0mm for CN 54.8 x 29.5 x 44.9mm for Multi Wall-Mount Plug Version (EU, USA, AUS and UK)	
Weight	70g max.	
Regulatory Approvals		
Approvals	Europe International USA & Canada Australia & New Zealand Korea China Japan India Russia (Customs Union) India	CE CB cULus / cETLus RCM / SAA KC CCC PSE BIS EAC BIS

Germany/Headquarters

RRC power solutions GmbH
Technologiepark 1
66424 Homburg / Saar

Tel.: +49 6841 98090
Fax: +49 6841 9809280
Email: sales@rrc-ps.de
Web: www.rrc-ps.de

USA

RRC power solutions Inc.
18340 Yorba Linda Blvd.,
107-437 Yorba Linda,
CA 92886-4104

Tel.: +1 714 777 3604
Fax: +1 714 777 3658
Email: usa@rrc-ps.com
Web: www.rrc-ps.com

Hong Kong

RRC power solutions Ltd.
S-V,6/F, Valiant Industrial
Centre 2-12 Au Pui Wan Street
Fo Tan, N.T., Hong Kong

Tel.: +852 2376 0106
Fax: +852 2375 0107
Email: hkrrc@rrc-ps.cn
Web: www.rrc-ps.com

China

RRC power solutions Ltd.
Room 1306, C Building,
Tianan International building,
Renmin South Road, Luohu
District, Shenzhen 518021

Tel.: +86 755 8374 1908
Fax: +86 755 8374 1861
Email: hkrrc@rrc-ps.cn
Web: www.rrc-ps.com