




1 AMP





3 AMP



6 AMP & 10 AMP



16 AMP



PPF 4200	Rated Current A	Leakage Current @ 250V 50Hz	Inductance mH			Connections	Resistor Value MΩ	Approvals		
			L1	L2	L3					
PPF 4200-1/01	1	0.2mA	4.3	4.3		6.3 x 0.8 Faston	1	■	■	■
PPF 4200-3/01	3	0.2mA	2.2	2.2		6.3 x 0.8 Faston	1	■	■	■
PPF 4200-6/01	6	0.2mA	1.3	1.3		6.3 x 0.8 Faston	1	■	■	■
PPF 4200-10/01	10	0.2mA	1.0	1.0		6.3 x 0.8 Faston	1	■	■	■
PPF 4200-16/01	16	0.2mA	0.45	0.45		6.3 x 0.8 Faston	1	■	■	■
Earth Line Choke Version										
PPF 4200E-1/01	1	0.2mA	4.3	4.3	0.3	6.3 x 0.8 Faston	1	■	■	■
PPF 4200E-3/01	3	0.2mA	2.2	2.2	0.3	6.3 x 0.8 Faston	1	■	■	■
PPF 4200E-6/01	6	0.2mA	1.3	1.3	0.3	6.3 x 0.8 Faston	1	■	■	■
PPF 4200E-10/01	10	0.2mA	1.0	1.0	0.3	6.3 x 0.8 Faston	1	■	■	■
PPF 4200E-16/01	16	0.2mA	0.45	0.45	0.3	6.3 x 0.8 Faston	1	■	■	■


Temperature Range: -25°C to +85°C
Operating Voltage: 250Vac
Operating Frequency: 0 to 400Hz
Test Voltage: L+N to ground, 2700Vdc, 2 seconds

Varistor 1,3 & 6 Amp
 Zinc oxide type; energy absorption 21 Joules (current impulse defined in IEC 60-2 Section 6). Varistor voltage: 430Vdc (measured at 1mA); clamping voltage 710V at 10A


Varistor 10 & 16 Amp
 Zinc oxide type; energy absorption 43 Joules (current impulse defined in IEC 60-2 Section 6). Varistor voltage: 430Vdc (measured at 1mA); clamping voltage 710V at 25A

■ Approved □ Submitted for Approval

CIRCUIT DIAGRAMS



Earth Line Choke Version





Continued overleaf


DIMENSIONS

All dimensions are nominal and in mm


PPF 4200 - 1/01 & 2/01



PPF4200 -10/01 & 16/01



PPF4200E -1/01,3/01,6/01,10/01 & 16/01



For further information on other ranges of **Belling Lee** EMC Filters please contact our sales office:

Tel: +44(0)1638 665161 Fax: +44(0)1638 660718

e-mail: sales@blpcomp.com

