Adapter Straight BNC Jack to Jack

multicomp PRO

RoHS Compliant



Specifications:

Connector Type
Body Style
Convert From Connector
Convert From Gender
Material

Electrical


Frequency Range Nominal Impedance Voltage Rating

Environmental

Operating Temperature Range

- : Intra Series Coaxial
- : Straight Adapter : BNC Coaxial
- : Plug
- : Brass
- : DC-4GHz
- : 50Ω
- : 500V Max.
- . 500 v Ivia
- : -40°C to +60°C

Diagram



Dimensions : Millimetres (Inches)

No	Description	Material	Qty	Finish
1	Body	Brass	1	Nickel 100µ" MIn.
2	Center Contact	Brass	1	Gold
3	Insulation	POM	2	None
4	Washer	Brass	1	Nickel

Part Number Table

Description	Part Number
RF/Coaxial Adapter, BNC Jack to BNC Jack	SPC20106

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

