

# SC Duplex Adapters


**RoHS  
Compliant**



### Specifications:

Wavelength	: (850nm, 1,310nm)
Insertion Loss	: Ceramic <=0.15dB, Metal <=0.2dB
Retentions Force	: 200 to 600g
Durability	: 500 mating
Operating Temperature	: -40°C to 80°C

### Diagram



**Recommended  
Mounting Hole  
(Panel Thickness is 1.7mm Max.)**

Dimensions : Millimetres

### Part Number Table

Description	Sleeve	Body		Mount Plate	Dust Cap	Part Number
	Type	Type	Colour	Type	Colour	
SC Adapter, Duplex	Metal	Plastic	Beige	Stainless Steel	Beige	SPC22792
		Metal Housing with Nickel Plating				SPC22794
		Plastic	Aqua Blue			SPC22795
	Ceramic	Plastic	Blue		Blue	SPC22797
		Metal Housing with Nickel Plating			Blue	SPC22799

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.