PCB Terminal Block Modular

multicomp PRO

RoHS

Compliant



Specifications:

Pitch Poles Housing Material Cage Clamp Contact Screw Thread Wire Size PCB Hole Diameter Tightening Torque, Max. Operating Temperature


Technical Data:

Nominal Current I_N Nominal Cross Section Maximum Load Current Insulating Material Nominal Voltage Nominal Current : 5mm : 2 to 3Poles : PA 66 : Brass, Ni Plated : Brass, Tin Plated : M2.6, Steel, Zinc Plated : 10AWG to 24AWG : 1.5mm : 6Lb-in : -40°C to +105°C

: 25A : 4mm² : 25A : PA : 300V : 25A

Diagram





Part Number Table

Description	Part Number
Terminal Block Eurostyle 10-24AWG	MB422-500MA02
	MB422-500MA03
	MB422-500MA04
	MB422-500MA08
	MB422-500MA12

Dimensions : Millimetres (Inches)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

