


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0194360413**  
**Status:** **Active**  
**Overview:** MX150L Industrial Sealed Connector System  
**Description:** MX150L 4 Circuit Rear Mount Flange Sealed Panel Mount Plug for 10-12 AWG Wire, without Gasket, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-19436-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-19432-001-001 (PDF)</a>	



*Series image - Reference only*

**General**

Product Family	Crimp Housings
Series	<u>19436</u>
Application	Power, Wire-to-Wire
Comments	Mat Seal Color Yellow, Polarized to Mating Part. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec
Overview	<u>MX150L Industrial Sealed Connector System</u>
Product Name	MX150L
UPC	800756731865

**Physical**

Circuits (maximum)	4
Circuits Detail	2x2
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	7.62mm
Pitch - Termination Interface	7.62mm
Polarized to Mating Part	No
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +125°C

**Electrical**

Current - Maximum per Contact	40.0A
-------------------------------	-------

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-19436-001
Product Specification	PS-19432-001-001
Sales Drawing	SD-19436-002

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - D(2020)4578-DC (25 June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

19436 Series

**Mates With**

19432 Receptacle

**Use With**