TE Internal #: 6-2176455-2

Surface Mount Resistors, Precision Resistor, 2 Termination, 0402, Taped & Reeled, .1%, Thin Film, Resistance Range  $1k\Omega-1M\Omega$   $\Omega$ ,

475K Ω, .063 W

View on TE.com >



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Number of Terminations: 2

Surface Mount Resistor Size Code: 0402

Surface Mount Resistor Packaging Method: Taped & Reeled

Surface Mount Resistor Tolerance: .1%

### **Features**

## **Product Type Features**

Product Type	Fixed Resistor
Resistor Type	Precision Resistor
Surface Mount Resistor Size Code	0402
Element Type	Thin Film

# **Configuration Features**

Number of Resistors	1
---------------------	---

### **Electrical Characteristics**

Voltage Rating	25 V
Surface Mount Resistor Tolerance	.1%
Resistance Range	$1k\Omega - 1M\Omega$ Ω
Surface Mount Resistor Resistance	475K Ω
Surface Mount Resistor Power Rating	.063 W

#### **Termination Features**

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

#### Mechanical Attachment

Mount Style Surface Mount
---------------------------



#### **Dimensions**

Surface Mount Resistor Dimensions	1 x .5 x .3 mm
Usage Conditions	
Temperature Coefficient	±25 ppm/°C
Packaging Features	
Surface Mount Resistor Packaging Method	Taped & Reeled

## **Product Compliance**

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# Compatible Parts





# Customers Also Bought



TE Model / Part #9-2176407-5 3560 100R 5%



TE Model / Part #8-2176407-3 3560 10R 5%



TE Model / Part #1SNK705062R0000 ZK2.5-RD





TE Model / Part #9-2176407-2 3560 56R 5%



TE Model / Part #6-104069-1 16 sys 50 hdr drra shrd sn



TE Model / Part #1-487937-6
FFC Receptacle Housing: 1.27mm







## **Documents**

Product Drawings
CPF 0402 475K 0.1% 25ppm 1K RL

English

Datasheets & Catalog Pages

CPF-1016

English