Plug BNC, Crimp, 75R





Specifications:

Connector Type : BNC Coaxial
Body Style : Straight Plug

Coaxial Termination : Crimp Impedance : 75Ω **Contact Material** : Brass Contact Plating : Gold Frequency Max. : 11GHz Connector Mounting : Cable **Body Plating** : Nickel Cable Diameter Max. : 5.1mm Coaxial Type : BT2002 : 1.5mΩ Contact Resistance DC Current Max. : 1A

Material : Brass with Silicone Gaskets

Operating Temperature : -65°C to +165°C

Proof Voltage : 2kV VSWR : 1.35 Working Voltage : 500V

Bodies : Brass per JIS-C3604
Centre Contact : Brass per JIS-C3604
Insulation : PTFE per ASTM D1457 and

ASTM D1710


Crimp Ferrule : Brass per JIS-C2700

Part to be clean and free of burrs



Plug BNC, Crimp, 75R





Description	Material	Finish	
Body	Brass	· Nickel 100μ" Min.	
Washer	DIdSS		
Spring Washer	SK-5		
Washer	Brass		
Gasket	Rubber	None	
Insulation	PTFE		
Shell	Zinc	Nickel 100u" Min	
Crimp Ferrule	Brass	Nickel 100µ" Min.	
Centre Contact		Gold	

Part Number Table

Description	Part Number
Plug, BNC, Crimp, 75R, 2002, NI	MP-13-10-4

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

