

www.vishay.com

Vishay Siliconix

Automotive N-Channel 40 V (D-S) 175 °C MOSFET



PRODUCT SUMMARY						
V _{DS} (V)	40					
$R_{DS(on)}(\Omega)$ at $V_{GS} = 10 \text{ V}$	0.0028					
$R_{DS(on)}$ (Ω) at $V_{GS} = 4.5 \text{ V}$	0.0042					
I _D (A)	175					
Configuration	Single					
Package	PowerPAK SO-8L					

FEATURES

- TrenchFET® Gen IV power MOSFET
- AEC-Q101 qualified
- 100 % Rq and UIS tested
- Material categorization: for definitions of compliance please see www.vishav.com/doc?99912



ı. L.	
G O	†
N-Channel MOSFET	

ABSOLUTE MAXIMUM RATINGS	(1C = 25 C, unless)	otherwise noted	1)		
PARAMETER		SYMBOL	LIMIT	UNIT	
Drain-source voltage		V_{DS}	40	V	
Gate-source voltage		V_{GS}	± 20		
Continuous drain current	T _C = 25 °C	1	175		
	T _C = 125 °C	I _D	102		
Continuous source current (diode conduction)		I _S	158	Α	
Pulsed drain current ^a		I _{DM}	450	1	
Single pulse avalanche current	L = 0.1 mH	I _{AS}	18.5		
Single pulse avalanche energy	L=0.11IIII	E _{AS}	17	mJ	
Maximum power dissipation ^a	T _C = 25 °C	D	190	w	
	T _C = 125 °C	P_{D}	63		
Operating junction and storage temperature range Soldering recommendations (peak temperature) c		T _J , T _{stg}	-55 to +175	°C	
			260		

THERMAL RESISTANCE RATINGS						
PARAMETER		SYMBOL	LIMIT	UNIT		
Junction-to-ambient	PCB mount b	R _{thJA}	68	°C/W		
Junction-to-case (drain)	case (drain)		0.79	C/VV		

Notes

- a. Pulse test; pulse width \leq 300 μ s, duty cycle \leq 2 %
- b. When mounted on 1" square PCB (FR4 material)
- c. See solder profile (www.vishay.com/doc?73257). The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection



www.vishay.com

Vishay Siliconix

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT	
Static					•			
Drain-source breakdown voltage	V _{DS}	$V_{GS} = 0$, $I_D = 250 \mu A$		40	-	-	V	
Gate-source threshold voltage	V _{GS(th)}	V _{DS} =	= V _{GS} , I _D = 250 μA	1.2	1.7	2.2	V	
Gate-source leakage	I _{GSS}	V _{DS} =	0 V, V _{GS} = ± 20 V	-	-	± 100	nA	
		$V_{GS} = 0 V$	V _{DS} = 40 V	-	-	1		
Zero gate voltage drain current	I _{DSS}	V _{GS} = 0 V	V _{DS} = 40 V, T _J = 125 °C	-	-	50	μΑ	
		V _{GS} = 0 V	V _{DS} = 40 V, T _J = 175 °C	-	-	250	1	
On-state drain current a	I _{D(on)}	V _{GS} = 10 V	V _{DS} ≥ 5 V	30	-	-	Α	
		V _{GS} = 10 V	I _D = 10 A	-	0.0022	0.0028	1	
B		V _{GS} = 10 V	I _D = 10 A, T _J = 125 °C	-	-	0.0051		
Drain-source on-state resistance a	R _{DS(on)}	V _{GS} = 10 V	I _D = 10 A, T _J = 175 °C	-	-	0.0062	Ω	
		V _{GS} = 4.5 V	I _D = 10 A	-	0.0032	0.0042		
Forward transconductance b	9 _{fs}	V _{DS} = 15 V, I _D = 10 A		-	70	-	S	
Dynamic ^b					•			
Input capacitance	C _{iss}			-	2150	3015		
Output capacitance	C _{oss}	$V_{GS} = 0 V$	V _{DS} = 25 V, f = 1 MHz	-	740	1040	pF	
Reverse transfer capacitance	C _{rss}			-	47	66		
Total gate charge c	Q_{g}			-	39	55		
Gate-source charge c	Q_{gs}	V _{GS} = 10 V	$V_{GS} = 10 \text{ V}$ $V_{DS} = 20 \text{ V}, I_{D} = 40 \text{ A}$		6	-	nC	
Gate-drain charge ^c	Q_{gd}			-	7	-	1	
Gate resistance	R_{g}	f = 1 MHz		1.5	3.2	5.1	Ω	
Turn-on delay time ^c	t _{d(on)}			-	10	15		
Rise time ^c	t _r	V _{DD} =	= 20 V, $R_1 = 2.0 \Omega$	-	4	7	1	
Turn-off delay time ^c	t _{d(off)}	$I_D \cong 10 \text{ A}, V_{GEN} = 10 \text{ V}, R_g = 1 \Omega$		-	33	50	ns	
Fall time ^c	t _f			-	10	15		
Source-Drain Diode Ratings and Cha	aracteristics b				•			
Pulsed current ^a	I _{SM}			-	-	600	Α	
Forward voltage	V_{SD}	I _F = 15 A, V _{GS} = 0 V		-	-	1.1	V	
Body diode reverse recovery time	t _{rr}	I _F = 10 A, di/dt = 100 A/μs		-	33	50	ns	
Body diode reverse recovery charge	Q _{rr}			-	21	31	nC	
Reverse recovery fall time	t _a			-	15	23		
Reverse recovery rise time	t _b			-	18	27	ns	
Body diode peak reverse recovery current	I _{RM(REC)}			-	1.1	1.8	Α	


Notes

- a. Pulse test; pulse width \leq 300 μ s, duty cycle \leq 2 %
- b. Guaranteed by design, not subject to production testing
- c. Independent of operating temperature


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Output Characteristics




Transconductance






Transfer Characteristics




On-Resistance vs. Drain Current







TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




On-Resistance vs. Junction Temperature




Source Drain Diode Forward Voltage






Drain Source Breakdown vs. Junction Temperature



On-Resistance vs. Gate-to Source Voltage



Safe Operating Area


Note

a. V_{GS} > minimum V_{GS} at which R_{DS(on)} is specified


For technical questions, contact: automostech



TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case

Note


- The characteristics shown in the two graphs
 - Normalized Transient Thermal Impedance Junction-to-Ambient (25 °C)
 - Normalized Transient Thermal Impedance Junction-to-Case (25 °C)

are given for general guidelines only to enable the user to get a "ball park" indication of part capabilities. The data are extracted from single pulse transient thermal impedance characteristics which are developed from empirical measurements. The latter is valid for the part mounted on printed circuit board - FR4, size 1" x 1" x 0.062", double sided with 2 oz. copper, 100 % on both sides. The part capabilities can widely vary depending on actual application parameters and operating conditions

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?77549.



PowerPAK® SO-8L Case Outline 3



DIM.		MILLIMETERS		INCHES			
DIM.	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.	
А	1.00	1.05	1.10	0.039	0.041	0.043	
A1	0.00		0.127	0.000		0.005	
A2	0.40	0.45	0.50	0.016	0.018	0.020	
b	0.33	0.41	0.49	0.013	0.016	0.019	
b1	0.43	0.51	0.59	0.017	0.020	0.023	
b2	4.00	4.10	4.20	0.157	0.161	0.165	
С	0.15	0.20	0.25	0.006	0.008	0.010	
D1	4.80	4.90	5.00	0.189	0.193	0.197	
D2	3.86	3.96	4.06	0.152	0.156	0.160	
D5	0.51	0.61	0.71	0.020	0.024	0.028	
D6	2.64	2.74	2.84	0.104	0.108	0.112	
е		1.27 BSC		0.050 BSC			
E	6.05	6.15	6.25	0.238	0.242	0.246	
E1	4.27	4.37	4.47	0.168	0.172	0.176	
E2	3.18	3.28	3.38	0.125	0.129	0.133	
E3	3.48	3.58	3.68	0.137	0.141	0.145	
E4	2.72	2.82	2.92	0.107	0.111	0.115	
E5	0.71	0.81	0.91	0.028	0.032	0.036	
L	0.62	0.72	0.82	0.024	0.028	0.032	
L1	0.92	1.07	1.22	0.036	0.042	0.048	
W1	0.31	0.41	0.51	0.012	0.016	0.020	
W4	0.31	0.36	0.41	0.012	0.014	0.016	
z1	0.37	0.47	0.57	0.015	0.019	0.022	
z2	0.99	1.09	1.19	0.039	0.043	0.047	
θ	0°		5°	0°		5°	

ECN: S19-0643-Rev. B, 05-Aug-2019


DWG: 6067 **Note**

• Millimeter will govern

Revison: 05-Aug-2019 1 Document Number: 76666



Recommended Land Pattern PowerPAK® SO-8L Single Short Ear



Dimensions in Millimeters (Inches)



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.