



555E

Product no.: 555E


Tip cutter - angled narrow head



The angled head provides for precise cuts at different working angles.



Narrow, robust head, suitable for working with high cutting force in confined areas.



[source images](#)

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 500 Micro is a full range of medium sized, robust, precision cutters with a wide range of head shapes. The cutters are manufactured from high grade tool steel. The cutting edges are hardened to Rockwell 63-65 HRC. The precision cutters have a nonreflecting surface, are ESD safe and resharable.

		Type	Type of Cut	Cutting Capacity
		Series 500 Medium		
		mm 0,03 0,1 0,2 0,3 0,4 0,5 0,6 0,7 0,8 0,9 1,0 1,1 1,2 1,3 1,4 1,5 1,6 1,7 1,8 1,9 2,0		
		Inch .0001 .0003 .0007 .0011 .0015 .0019 .0023 .0027 .0031 .0035 .0039 .0043 .0047 .0051 .0055 .0059 .0062 .0066 .0070 .0074 .0078		
	512N		Semi Flush	
	512E		Semi Flush	
	599T		Semi Flush / Carbide	
	522N		Flush	
	599E		Flush	
	532N		Super Full Flush	
	576TX1		Flush / Carbide	
	503E		Flush	
	503ETST 30°		Flush / Carbide	
	504AE		Flush	
	555E		Flush	
	572E		Flush	
	582E		Flush	
	593AE		Flush	
	575E		Flush	
	592E		Flush	
	792E		Super Full Flush	
	576TX		Flush / Carbide	
	570E		Flush	
	573E		Flush	
				for vertical tip cutting





Technical Data

Length mm	120
Length of cutting edges mm	7
Head width mm	11
Head thickness mm	6
Head length mm	28.6
Max. cutting capability – hard wire mm	---
Weight in oz	2.399
Length of cutting edges Inches	0.276
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	1.126
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,6
Max. cutting capability – copper wire mm	Ø 1,3
Length inches	4.724
Weight in g	68
Erem applications	Microelectronic