

Pb Free RoHS

4 Pad 2.0mm x 1.6mm SMD, LVCMOS Oscillator, 32.768kHz

ISM36 Series

Product Features:

- LVCMOS compatible output
- Low 50µA Input Current
- Small Footprint SMD Package
- AT Cut Temperature Stability Characteristic
- Six supply voltages options, 1.8V, 2.5V, 2.8V, 3.0V, 3.3V, 1.62V to 3.63V (Continuous)
- RoHS and REACH compliant

Typical Applications:

- Real Time Clock Source
- Metering
- Industrial Control
- System Clock

ELECTRICAL SPECIFICAT			
Frequency Range	32.768kHz		
Frequency Stability	±25ppm Maximum ±50ppm Maximum ±100ppm Maximum	Inclusive of Initial Tolerance, Stability over Operating Temperature Range, Load (±5%), Voltage (±5%), and Aging (First Year at +25°C)	
Operating Temperature Range	0°C to +70°C -20°C to +70°C -40°C to +85°C		
Supply Voltage (Vdd)	1.8V, 2.5V, 2.8V, 3.0V, 3.3V, or 1.62V to 3.63V		
Input Current	50μA Typical, 100μA Maximum	No Load, Vdd = 3.3V	
Output Logic Type	LVCMOS		
Output Drive Capability	15pF Maximum		
Aging	±3ppm/year Maximum	at +25°C	
Duty Cycle	50 ±5(%)	Measured at 50% of waveform	
Rise / Fall Time	15nSec Maximum	Measured from 10% to 90% of waveform	
Output Voltage Logic High	90% of Vdd Minimum		
Output Voltage Logic Low	10% of Vdd Maximum		
Input Voltage Logic High	70% of Vdd Minimum or No Connect to Enable Output		
Input Voltage Logic Low	30% of Vdd Maximum to Disable Output (High Impedance)		
Standby Current	1μA Typical, 3μA Maximum	Disabled Output: High Impedance	
Startup Time	2mSec Maximum		
• All minimum and maximum limits are specified over temperature and rated operating voltage with 15pF output unless otherwise stated. • A 0.1µF bypass capacitor is recommended between Vdd (pad 4) and GND (pad 2) to minimize power supply noise.			

ARCOLUTE MAYIMUM LIMITS				
ABSOLUTE MAXIMUM LIMITS				
Storage Temperature Range	-55°C to +125°C			
Supply Voltage Range	-0.3Vdc to Vdd +0.5Vdc			
Electrostatic Discharge	2000V Maximum			
Solder Temperature	260°C Maximum			
Junction Temperature	150°C Maximum			
NOTE: If the post is used housed should be regiment until so it may come internal destruction. The year objected by used under the green and of				

NOTE: If the part is used beyond absolute maximum ratings, it may cause internal destruction. The part should be used under the recommended operating conditions or the reliability of this part may be damaged if those conditions are exceeded.

PART NUMBER GUIDE							
Series	Supply Voltage	Operating Temperature Range	Frequency Stability	Pin 1 Connection	Frequency		
ISM36-	1 = 1.8V	1 = 0°C to +70°C	A = ±25ppm	H = Tri-State (High Impedance)	-32.768 kHz		
	6 = 2.5V	3 = -20°C to +70°C	$B = \pm 50$ ppm				
	2 = 2.8V	2 = -40°C to +85°C	C = ±100ppm				
	7 = 3.0V						
	3 = 3.3V						
	8 = 1.62V to 3.63V						
Sample Part Number: ISM36-82BH-32.768 kHz							


Rev: 07/08/19_C



4 Pad 2.0mm x 1.6mm SMD, LVCMOS Oscillator, 32.768kHz



ISM36 Series



MARKING

Line 1: 32.768

Line 2: Date Code (YWW)

Pin 1 Dot


PACKAGE INFORMATION


Termination = e4 (Au over Ni over W base metallization)

Terminal Plating Thickness:

Gold (0.3µm to 1.0µm), Nickel (1.27µm to 8.89µm)

ENVIRONMENTAL SPECIFICATIONS			
Mechanical Shock	MIL-STD-202, Method 213		
Mechanical Vibration	MIL-STD-202, Method 204		
Resistance to Soldering Heat	MIL-STD-202, Method 210		
Solderability	J-STD-002		
Gross Leak	MIL-STD-883, Method 1014		
Fine Leak	MIL-STD-883, Method 1014		
Moisture Sensitivity Level	MSL 1 (+260°C)		







QUALITY SYSTEM CERTIFIED = ISO 9001 = ILSI America Phone 775-851-8880 ● Fax 775-851-8882 ●email: e-mail@ilsiamerica.com ● www.ilsiamerica.com

Rev: 07/08/19_C



ISM36 Series





PROPRIETARY AND CONFIDENTIAL

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION, AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE NOR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM ILSI America.

Rev: 07/08/19_C