


SVxx20xxQ series

Description

The SVxx20xxQ high temperature SCR series is ideal for uni-directional switch applications such as phase control in heating, motor speed controls, converters/rectifiers and inrush current controllers.

These SCRs have a low gate current, (I_{GT}) trigger level of 6mA and 10mA maximum at approximately 1.5V for SVxx20x1Q and SVxx20x2Q, respectively.

Features & Benefits

- Halogen free and RoHS compliant
- 150 °C maximum junction temperature
- Surge capability up to 300A at 60 Hz half cycle
- High dv/dt performance
- Low turn off time

Applications


Typical applications include AC Generator (ACG) rectifiers, battery voltage regulators, generic converters and inrush current controller in various AC to DC applications. Additional applications include controls for power tools, home/brown good and white goods appliances.

Internally constructed isolated packages offered for ease of heat sinking with high isolation voltage.

Main Features

Symbol	Value	Unit
$I_{(RMS)}$	20	A
V_{DRM}/V_{RRM}	600	V
I_{GT}	6 to 10	mA

Schematic Symbol



Absolute Maximum Ratings – 20A SCR

Symbol	Parameter	Test Conditions		Value	Unit
V_{DSM}/V_{RSM}	Peak non-repetitive blocking voltage	$P_w = 100 \mu s$		800	V
$I_{T(RMS)}$	RMS on-state current	SVxx20LxQ	$T_c = 105^\circ C$	20	A
		SVxx20RxQ SVxx20NxQ	$T_c = 130^\circ C$		
$I_{T(AV)}$	Average on-state current	SVxx20LxQ	$T_c = 105^\circ C$	12.8	A
		SVxx20RxQ SVxx20NxQ	$T_c = 130^\circ C$		
I_{TSM}	Peak non-repetitive surge current	single half cycle; $f = 50Hz$; T_j (initial) = 25 °C		250	A
		single half cycle; $f = 60Hz$; T_j (initial) = 25 °C		300	
I^{2t}	I^{2t} Value for fusing	$t_p = 8.3 ms$		374	A^2s
dI/dt	Critical rate of rise of on-state current	$f = 60Hz$; $T_j = 150^\circ C$		125	$A/\mu s$
I_{GM}	Peak gate current	$T_j = 150^\circ C$		4	A
$P_{G(AV)}$	Average gate power dissipation	$T_j = 150^\circ C$		0.8	W
T_{stg}	Storage temperature range			-40 to 150	°C
T_j	Operating junction temperature range			-40 to 150	°C

Note: xx=voltage/10, x=sensitivity

Electrical Characteristics ($T_j = 25^\circ C$, unless otherwise specified)

Symbol	Test Conditions		$SVxx20x1Q$	$SVxx20x2Q$	Unit
I_{GT}	$V_D = 12V$; $R_L = 60 \Omega$	MIN.	3.8	5	mA
		MAX.	6	10	
		MAX.	1.5	1.5	
V_{GT}	$V_D = 67\% V_{DRM}$; gate open; $T_j = 125^\circ C$	MIN.	400	800	V/μs
			200	400	
V_{GD}	$V_D = V_{DRM}$; $R_L = 3.3 k\Omega$; $T_j = 110^\circ C$	MIN.	0.2	0.2	V
I_H	$I_T = 200mA$ (initial)	MAX.	25	40	mA
t_q	$I_T=2A$; $t_p=50\mu s$; $dv/dt=5V/\mu s$; $dI/dt=-30A/\mu s$	MAX.	12	12	μs
t_{gt}	$I_G = 2 \times I_{GT}$ PW = 15μs $I_T = 40A$	TYP.	2.6	2.6	μs

Static Characteristics

Symbol	Test Conditions		Value	Unit
V_{TM}	$I_T = 40A$; $t_p = 380\mu s$	MAX.	1.65	V
			10	μA
		MAX.	1000	
			4000	

Thermal Resistances

Symbol	Parameter		Value	Unit
R_{ThetaC}	Junction to case (AC)	$SVxx20RxQ$ $SVxx20NxQ$	1.0	°C/W
		$SVxx20LxQ$	2.5	

Note: xx=voltage/10, x=sensitivity

Figure 1: Normalized DC Gate Trigger Current vs. Junction Temperature




Figure 2: Normalized DC Gate Trigger Voltage vs. Junction Temperature




Figure 3: Normalized DC Holding Current vs. Junction Temperature




Figure 4: On-State Current vs. On-State Voltage (Typical)




Figure 5: Power Dissipation (Typical) vs. RMS On-State Current




Figure 6: Maximum Allowable Case Temperature vs. RMS On-State Current




Figure 7: Maximum Allowable Case Temperature vs. Average On-State Current




Figure 8: Peak Capacitor Discharge Current




Figure 9: Peak Capacitor Discharge Current Derating





Figure 10: Surge Peak On-State Current vs. Number of Cycles




SUPPLY FREQUENCY: 60 Hz Sinusoidal
 LOAD: Resistive
 RMS On-State Current: $[I_{(IRMS)}]$: Maximum Rated Value at Specified Case Temperature

Notes:

1. Gate control may be lost during and immediately following surge current interval.
2. Overload may not be repeated until junction temperature has returned to steady-state rated value.

Soldering Parameters

Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 180 secs
Average ramp up rate (Liquidus Temp) (T_L) to peak		
$T_{s(max)}$ to T_L - Ramp-up Rate		
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Time (t_L)	60 – 150 seconds
Peak Temperature (T_p)		
Time within 5°C of actual peak Temperature (t_p)		
Ramp-down Rate		
Time 25°C to peak Temperature (T_p)		
Do not exceed		
280°C		



Physical Specifications

Terminal Finish	100% Matte Tin-plated
Body Material	UL Recognized compound meeting flammability rating V-0
Lead Material	Copper Alloy


Design Considerations

Careful selection of the correct component for the application's operating parameters and environment will go a long way toward extending the operating life of the Thyristor. Good design practice should limit the maximum continuous current through the main terminals to 75% of the component rating. Other ways to ensure long life for a power discrete semiconductor are proper heat sinking and selection of voltage ratings for worst case conditions. Overheating, overvoltage (including dv/dt), and surge currents are the main killers of semiconductors. Correct mounting, soldering, and forming of the leads also help protect against component damage.

Environmental Specifications


Test	Specifications and Conditions
AC Blocking	MIL-STD-750, M-1040, Cond A Applied Peak AC voltage @ 150°C for 1008 hours
Temperature Cycling	MIL-STD-750, M-1051, 1000 cycles; -55°C to +150°C; 15-min dwell-time
Temperature/Humidity	EIA / JEDEC, JESD22-A101 1008 hours; 160V - DC: 85°C; 85% rel humidity
Resistance to Solder Heat	MIL-STD-750 Method 2031
Solderability	ANSI/J-STD-002, category 3, Test A
Lead Bend	MIL-STD-750, M-2036 Cond E
Moisture Sensitivity Level	Level 1, JEDEC-J-STD-020D

Dimensions — TO-220AB (L-Package) — Isolated Mounting Tab




Dimension	Inches		Millimeters	
	Min	Max	Min	Max
A	0.380	0.420	9.65	10.67
B	0.105	0.115	2.67	2.92
C	0.230	0.250	5.84	6.35
D	0.590	0.620	14.99	15.75
E	0.142	0.147	3.61	3.73
F	0.110	0.130	2.79	3.30
G	0.540	0.575	13.72	14.61
H	0.025	0.035	0.64	0.89
J	0.195	0.205	4.95	5.21
K	0.095	0.105	2.41	2.67
L	0.060	0.075	1.52	1.91
M	0.085	0.095	2.16	2.41
N	0.018	0.024	0.46	0.61
O	0.178	0.188	4.52	4.78
P	0.045	0.060	1.14	1.52
R	0.038	0.048	0.97	1.22

Dimensions — TO-220AB (R-Package) — Non-Isolated Mounting Tab Common with Center Lead



Dimension	Inches		Millimeters	
	Min	Max	Min	Max
A	0.380	0.420	9.65	10.67
B	0.105	0.115	2.67	2.92
C	0.230	0.250	5.84	6.35
D	0.590	0.620	14.99	15.75
E	0.142	0.147	3.61	3.73
F	0.110	0.130	2.79	3.30
G	0.540	0.575	13.72	14.61
H	0.025	0.035	0.64	0.89
J	0.195	0.205	4.95	5.21
K	0.095	0.105	2.41	2.67
L	0.060	0.075	1.52	1.91
M	0.085	0.095	2.16	2.41
N	0.018	0.024	0.46	0.61
O	0.178	0.188	4.52	4.78
P	0.045	0.060	1.14	1.52
R	0.038	0.048	0.97	1.22

Dimensions – TO- 263AB (N-package) – D²-Pak Surface Mount



Dimension	Inches		Millimeters	
	Min	Max	Min	Max
A	0.360	0.370	9.14	9.40
B	0.380	0.420	9.65	10.67
C	0.178	0.188	4.52	4.78
D	0.025	0.035	0.64	0.89
E	0.045	0.060	1.14	1.52
F	0.060	0.075	1.52	1.91
G	0.095	0.105	2.41	2.67
H	0.092	0.102	2.34	2.59
J	0.018	0.024	0.46	0.61
K	0.090	0.110	2.29	2.79
S	0.590	0.625	14.99	15.88
V	0.035	0.045	0.89	1.14
U	0.002	0.010	0.05	0.25
W	0.040	0.070	1.02	1.78

Product Selector

Part Number	Voltage	Gate Sensitivity	Type	Package
	600V			
SVxx20L1Q	X	6mA	Standard SCR	TO-220L
SVxx20R1Q	X	6mA	Standard SCR	TO-220R
SVxx20N1Q	X	6mA	Standard SCR	TO-263
SVxx20L2Q	X	10mA	Standard SCR	TO-220L
SVxx20R2Q	X	10mA	Standard SCR	TO-220R
SVxx20N2Q	X	10mA	Standard SCR	TO-263


Note: xx = Voltage/10, x=sensitivity

Packing Options

Part Number	Marking	Weight	Packing Mode	Base Quantity
SVxx20LxQTP	SVxx20Lx	2.2g	Tube	1000 (50 per tube)
SVxx20RxQTP	SVxx20Rx	2.2g	Tube	1000 (50 per tube)
SVxx20NxQTP	SVxx20Nx	1.6g	Tube	1000 (50 per tube)
SVxx20NxQRP	SVxx20Nx	1.6g	Embossed Carrier	500


Note: xx=voltage/10, x=sensitivity

Part Numbering System



Part Marking System

T0-220 AB - (L and R Package)
T0-263 AB - (N Package)



TO-263 Embossed Carrier Reel Pack (RP) Specifications

Meets all EIA-481-2 Standards

