

TECHNICAL DATA SHEET

PRO-ELEC

RoHS
Compliant

BALANCED MULTICORE MICROPHONE CABLE

MODELS: PELB0580-PELB0581

APPLICATION

Balanced, multicore microphone cable, suitable for use in studio, stage and general A/V applications.



ELECTRICAL CHARACTERISTICS

Rated Temperature: 60°C

Conductor Resistance (Max. @ 20°C): 121.01Ω/km

CONSTRUCTION

Core Insulation	PE
Core Insulation Colours	Red White
Filler	PPR (16-core only)
Drain Wire	7/0.20mm
Wrap	Aluminium
Covering	PVC
Covering Colour	Blue
Jacket	PVC
Jacket Colour	Blue

DIMENSIONS

Cores	Conductors	Overall Dia.	Length	Model
8	20/0.10mm	10.00mm	50m	PELB0580
16		13.00mm		PELB0581

Important Notice: This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

PRO-ELEC