

Features


Regulated Converters

- Compact 10.3x7.5mm SMD package
- 5kVAC reinforced isolation
- 5V or 3.3V post-regulated, selectable outputs
- Low EMI emissions
- Ultrawide temperature range (-40°C to +140°C)
- Low profile (2.6mm)

RECOM
DC/DC Converter

RxxCTxx

0.5 Watt
16-Pin SOIC
Single Output



UL62368-1 (pending)
CSA/CAN C22.2 No. 62368-1 (pending)
IEC/EN62368-1 (pending)
IEC/EN60601-1 (pending)

Description

Low cost, low profile, 500mW SMD isolated DC/DC single output converter ideal for applications such as communication, current sensing, and medical applications which require robust isolation. The R05CT05S is a single solution with 5V input and a user-definable single, regulated 3.3V or 5V output. There is no minimum load requirement. Standard isolation is 5kVAC/1min with a 2MOPP rating for medical applications. The operating temperature is from -40°C up to +140°C with derating.


Selection Guide

Part Number	Input Voltage Range [VDC]	Selectable Output Voltage [VDC]	Output Power [mW]	Efficiency typ. [%]
R05CT05S	4.5-5.5	3.3, 3.7, 5 or 5.4	500	60

Notes:

Note1: nom. V_{IN} = 5VDC, V_{OUT} set to 5VDC, load = 100mA

Model Numbering



Notes:

Note1: add suffix "-CT" for bag packaging for more details refer to "PACKAGING INFORMATION" without suffix, standard tape and reel packaging

Specifications (measured @ T_a = 25°C, nom. V_{in} , full load and after warm-up unless otherwise stated)

ABSOLUTE MAXIMUM RATINGS ⁽²⁾				
Parameter	Condition	Min.	Typ.	Max.
Absolute Maximum Voltage	$+V_{IN}$ to $-V_{IN}$	-0.3VDC		6VDC
	CTRL, SYNC, SYNC_OK to $-V_{IN}$	-0.3VDC		$+V_{IN} + 3VDC$
	$+V_{OUT}$ to $-V_{OUT}$	-0.3VDC		6VDC
	SEL to $-V_{OUT}$	-0.3VDC		$V_{OUT} + 0.3VDC$
Operating IC Junction Temperature (T_J)		-40°C		+150°C
Operating Ambient Temperature (T_{AMB})		-40°C		+150°C
Storage Temperature (T_{STO})		-65°C		+150°C

Notes:


Note2: Stresses beyond those listed under absolute maximum ratings can cause permanent damage to the device. (Values are at non-operating)

Specifications (measured @ $T_a = 25^\circ\text{C}$, nom. V_{in} , full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS

Parameter	Condition	Min.	Typ.	Max.
Input Voltage Range	nom $+V_{in} = 5\text{VDC}$	4.5VDC	5VDC	5.5VDC
Under Voltage Lockout (UVLO)	DC-DC ON DC-DC OFF		3.7VDC 4.2VDC	
Under Voltage Lockout Hysteresis			0.5VDC	
Input Current Range		0mA		200mA
Quiescent Current	SEL pin shorted to V_{iso} ($V_{out} = 5\text{VDC}$)		45mA	
	SEL pin with $100\text{k}\Omega$ connected to V_{iso} ($V_{out} = 5.4\text{VDC}$)		40mA	
	SEL pin shorted to $-V_{out}$ ($V_{out} = 3.3\text{VDC}$)		80mA	
	SEL pin with $100\text{k}\Omega$ connected to $-V_{in}$ ($V_{out} = 3.7\text{VDC}$)		75mA	
Minimum Load		0%		
Start-up Time	power up using CTRL function		1.5ms 1.2ms	
Rise time			750 μs	
ON/OFF CTRL	DC-DC ON DC-DC OFF	0.8VDC		2.2VDC
Input Current of CTRL Pin	CTRL voltage = 5VDC		5 μA	10 μA
Standby Current	DC-DC OFF			100 μA
Internal Operating Frequency		7.2MHz	8MHz	8.8MHz
Output Ripple and Noise (20MHz BW)	10 $\mu\text{F} + 0.1\mu\text{F}$ V_{out} set to 5.4VDC, load = 90mA		50mVp-p	
	10 $\mu\text{F} + 0.1\mu\text{F}$ V_{out} set to 5.0VDC, load = 100mA			
	10 $\mu\text{F} + 0.1\mu\text{F}$ V_{out} set to 3.7VDC, load = 130mA			
	10 $\mu\text{F} + 0.1\mu\text{F}$ V_{out} set to 3.3VDC, load = 150mA			


Typical Application Circuit




CTRL	R_{TRIM}	V_{out_set}
high	shorted to $+V_{in}$	5.0VDC
high	$100\text{k}\Omega$ to $+V_{in}$	5.4VDC
high	shorted to $-V_{out}$	3.3VDC
high	$100\text{k}\Omega$ to $-V_{out}$	3.7VDC
high	open	unsupported
low	X	0VDC

Efficiency vs. Load

$V_{out} = 5.0\text{VDC}$




$V_{out} = 5.4\text{VDC}$



continued on next page

Specifications (measured @ $T_a = 25^\circ\text{C}$, nom. V_{in} , full load and after warm-up unless otherwise stated)



SYNC FUNCTION

Parameter	Condition	Min.	Typ.	Max.
SYNC Pin Input Current	SYNC Voltage= 5VDC		0.02 μA	1 μA
SYNC OK Output Voltage	I SYNC_OK= -2mA		150mV	
SYNC OK pin leakage current	V SYNC_OK= 5VDC			1 μA

Synchronous clock input pin. Provide a clock signal to synchronize multiple RxxCTxxS devices or connect to $-V_{IN}$ for standalone operation using the internal oscillator. If the SYNC pin is left open it should be separated from any switching noise to avoid false clock coupling.

Active-low, open-drain diagnostic output. Pin is asserted LOW if an no external SYNC clock or one that is outside of the operating range of the RxxCTxxS is detected. In this state, the external clock is ignored and the DC-DC converter is clocked by the device's internal oscillator. The pin is in high-impedance if a good clock is applied on SYNC.

REGULATION

Parameter	Condition	Min.	Typ.	Max.
Output Voltage Accuracy	V_{OUT} set to 5VDC; load= 0mA to 75mA, $V_{IN} = 4.5\text{VDC}$	4.7VDC	5VDC	5.3VDC
	V_{OUT} set to 5VDC; load= 0mA to 100mA, $V_{IN} \geq 5\text{VDC}$	4.7VDC	5VDC	5.3VDC
	V_{OUT} set to 5.4VDC; load= 0mA to 60mA, $V_{IN} = 4.5\text{VDC}$	5.1VDC	5.4VDC	5.7VDC
	V_{OUT} set to 5.4VDC; load= 0mA to 90mA, $V_{IN} \geq 5\text{VDC}$	5.1VDC	5.4VDC	5.7VDC
	V_{OUT} set to 3.3VDC; load= 0mA to 110mA, $V_{IN} = 4.5\text{VDC}$	3.1VDC	3.3VDC	3.5VDC
	V_{OUT} set to 3.3VDC; load= 0mA to 150mA, $V_{IN} \geq 5\text{VDC}$	3.1VDC	3.3VDC	3.5VDC
	V_{OUT} set to 3.7VDC; load= 0mA to 100mA, $V_{IN} = 4.5\text{VDC}$	3.5VDC	3.7VDC	3.9VDC
	V_{OUT} set to 3.7VDC; load= 0mA to 130mA, $V_{IN} \geq 5\text{VDC}$	3.5VDC	3.7VDC	3.9VDC
Line Regulation	low line to high line		1%	
Load Regulation	0% to 100% load		1.5%	

PROTECTIONS

Parameter	Condition	Values
Short Circuit Protection (SCP)		power limiting, continuous protection
Short Circuit Input Current	$V_{IN} = 4.5\text{VDC}$	215mA
	$V_{IN} = 5\text{VDC}$	240mA
	$V_{IN} = 5.5\text{VDC}$	260mA
Isolation Voltage	1 minute	5kVAC

continued on next page

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Parameter	Condition	Values
Maximum repetitive peak isolation voltage		1.414kV peak
Maximum working isolation voltage		1kVAC
		1.414kVDC
Maximum transient isolation voltage	1 minute	7.071kV peak
Maximum surge isolation voltage	according IEC62368-1= 1.2/50us	6.25kV peak
Isolation Resistance	25°C	10 ⁹ Ω typ.
Isolation Capacitance		3.5pF typ.
Insulation Grade		reinforced
Common mode transient immunity		±100V/ns
Internal Clearance		>0.12mm
External Creepage		>8mm

ENVIRONMENTAL


Parameter	Condition			Value
Operating Temperature Range	@ natural convection 0.1m/s	with derating without derating	refer to "Thermal Derating (5)"	-40°C to +140°C -40°C to + 55°C
ESD	human-body model (HBM), ANSI/ESDA/JEDEC JS-001			±1kV
	charged-device model (CDM), JEDEC JESD22-C101			±0.5kV
Moisture Sensitive Level	MSL peak temp. ⁽⁴⁾			Level 3, 260°C, 168hrs
Temperature Coefficient				50ppm/K
Thermal Impedance ⁽⁵⁾	junction to T _{AMB}			63.8K/W
	junction to case (top)			21.4K/W
	junction to case (bottom)			37.2K/W
	junction to board			38.5K/W
Operating Altitude				5000m
Operating Humidity				95% RH max.
Pollution Degree				PD2
MTBF	according to TR-332, 50% stress G.B.		+55°C	2500 x 10 ⁶ hours

Notes:

Note4: The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature

Note5: Tested with 54.0 x 85.6mm 2 layer PCB with 105µm copper

Thermal Derating ⁽⁵⁾




Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


DIMENSION AND PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Material	case	
Dimension (LxWxH)		
Weight		

Dimension Drawing (mm)



Recommended Footprint Details (Top View)



Pad Information

Pad #	Function
1	CTRL
2	-VIN
3	+VIN
4	SYNC
5	SYNC OK
6, 7, 8, 10, 11, 12	NC
9, 15, 16	-VOUT
13	TRIM
14	+VOUT

Tolerances: x.x= ±0.1mm
x.xx / x.xxx = ±0.05mm

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)	reel (diameter + width)	Ø330.0 + 16.4mm height
	tape and reel (carton)	350.0 x 350.0 x 43.0mm
	moisture barrier bag ("-CT")	100.0 x 100.0 x 30mm
Packaging Quantity	tape and reel	500pcs
	moisture barrier bag ("-CT")	10pcs
Storage Temperature Range		-65°C to +150°C

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.