
# > GND SeriesClassic Solid State RelaysPanel Mount - DC Output

- > Output current of 10 and 40 Amps
- > Output Voltage of 5-60 V and 5-200 V
- > Control voltage of 4-32 V
- > DC switching (DC loads)
- > Integrated IP20 touch-safe removable covers
- > Built-in overvoltage protection
- > LED input status indicator



DC Switching Version

Product Selection - DC switching (DC loads)			
Rated Load Current	10A	40A	
Output Voltage	5-200 V	5-60 V	
Control Voltage			
4-32 V	84137850N	84137870N	



Do you need an adapted or customized solution? Contact us on www.crouzet.com

#### Description:

Crouzet Solid State Relays are designed to be used in almost any application, offering very long life expectancy and are easy to install, easy to use, robust and multipurpose.

For more information about Crouzet's Solid State relays, please visit www.crouzet.com.



| WWW.CROUZET.COM | 2 | GND Series | 10/2020

Accessories		
Туре	Description	Part-Number
Heatsink	0.9 °C/W Thermal Resistance	26532752N
Heatsink	1.1 °C/W Thermal Resistance	26532753N
Heatsink	1.2 °C/W Thermal Resistance	26532754N
Heatsink	1.75 °C/W Thermal Resistance	26532755N
Heatsink	2.2 °C/W Thermal Resistance	26532756N
Adapter	DIN Rail	26532764N
Thermal Pad	Self-Adhesive Thermal Pad	26532722N
Screws	Screw Mounting Kit	26532001
Thermal Grease	Thermal Grease for Heatsink mounting	26532003

Output Specifications <sup>(1)</sup>		
Description	10A	40A
Maximum Load Current [Arms](3)	20	40
Minimum Load Current [mArms]	5	
Typical Operating Voltage [Vrms]	5-110 V	5-60 V
Min / Max Operating Voltage [Vrms]	5-200 V	5-60 V
Transient Voltage [Vpk]	200	100
Maximum Off-State Leakage Current @ Rated Voltage [mArms]	3	
Minimum Off-State dV/dt @ Maximum Rated Voltage [V/µsec]	N/A	
Non-repetitive peak overload current @ 100 ms [Apeak]	380 @t=0.1 ms	320 @t=0.1 ms
Maximum On-State Voltage Drop @ Rated Current [Vpeak]	0.97	1.05
Thermal Resistance Junction to Case (Rjc) [°C/W]	0.66	0.9
Minimum Heat Sink for Rated Current @ 40 °C [°C/W]	3.4	1.15

Input Specifications	
Description	4-32 V <del></del>
Input Voltage Range	4-32 V <sup>(4)</sup>
Maximum Reverse Voltage	-32 V
Minimum Turn-On Voltage	3.5 V
Must Turn-Off Voltage	1 V
Minimum Input Current (for on-state)	34 mA
Maximum Input Current [mA]	35 mA
Nominal Input Impedance [Ohms]	Current Limited
Maximum Turn-On Time [msec]	0.02
Maximum Turn-Off Time [msec]	0.02

General Specifications		
Description	10A	40A
Dielectric Strength, Input/Output to Ground (50/60 Hz)	2500 V	
Minimum Insulation Resistance (@ 500 V)	10°Ω	
Maximum Capacitance, Input/Output	8pf	
Ambient Operating Temperature Range	-25 to 90 °C	
Ambient Storage Temperature Range	-40 to 100 °C	
Weight (typical)	80 g	

General Specifications		
Description	10A	40A
Housing Material	UL94 V-0	
Baseplate Material	Aluminium	
Input Terminal Screw Torque Range (in-lb/Nm)	11-18 /1.2-2.0	
Load Terminal Screw Torque Range (in-lb/Nm)	18-26 / 2-3	
SSR Mounting Screw Torque Range (in-lb/Nm)	11-16 /1.2-1.8	
Humidity per IEC60068-2-78	40-85 %	
LED Input Status Indicator	Green	
MTBF (Mean Time Between Failures) at 40 °C ambient temperature <sup>(5)</sup>	25	
MTBF (Mean Time Between Failures) at 60 °C ambient temperature <sup>(5)</sup>	17	

# General Notes (1) All parameters at 25 °C unless otherwise specified

 $^{(4)} Increase$  minimum voltage by 1 V for operations from -20 to -40  $^{\circ} C$ 


<sup>(3)</sup>Heat sinking required, see derating curves

 $^{(5)}\!\text{All parameters at 50 \% power rating}$  and 100 % duty cycle (contact tech support for detailed report)

# Diagrams

#### Wiring

# GND



TERMINALS	WIRE SIZE		Terminal Screw
TERMINALS	SOLID	STRANDED	Torque (N.m)
Input	1814 AWG (0.752.5 mm²) 2 x 1814 AWG (0.752.5 mm²)	1814 AWG (0.752.5 mm²) 2 x 1814 AWG (0.752.5 mm²)	1.2 - 2
Output	168 AWG (1.510 mm²) 2 x 168 AWG (1.510 mm²)	168 AWG (1.56 mm²) 2 x 1610 AWG (1.56 mm²)	2 - 3

#### GND




Load


# Diagrams

# **Equivalent Circuit Block**

GND Series DC control without ouput protection




Input current vs Input Voltage Standard Regulated DC inputs




# Diagrams

#### Dimensions (mm)

GND front view





GND side view



#### Curves

# **Surge Current Information**





#### Curves

# **Thermal Derating Curves**

