



2,300 Watt Hot air gun HGE 23-650 LCD

- Precise hot air gun with LCD display for precise setting of temperature and air volume for different materials and applications
- Settings programmable to be retrieved for frequently recurring applications
- High-quality ceramic heating, powerful motor and optimum device cooling for long service life
- Wide range of uses: removal of varnish, shaping, crimping, welding and much more
- LCD temperature display for material-matched working
- Ergonomic design and handle with non-slip soft-grip surface provides convenient handling
- Safe stationary application due to large non-slip floor space

Order no.	603065000
EAN code	4061792185913

Air volume	150 / 500 l/min
Number of air volume levels	infinitely variable
Number of air temperature levels	infinitely variable
Weight (without power cable)	24,2 kg

Scope of delivery

Wide jet nozzle (50 mm), Wrap around nozzle

metaBOX 145 L, empty (626884000)

Order no. 626884000

EAN 4061792189157



Product may differ from Image

- Intelligent transport and storage system for mobile working
- Extremely robust and break-proof due to the material and design for maximum resilience
- Optimum protection of machine and accessories against dirt and moisture (IP43)
- Fast and easy stacking and coupling of the boxes in all system widths
- One box in the stack can easily be opened without having to decouple it
- A selection of two: Comfortable front handle for carrying the box near you and extra-wide cover handle to carry several stacked-up boxes
- Numerous tailor-made inserts (accessories) for individual order inside the box
- Clever accessories: Roller board and trolley for maximum mobility as well as an adapter plate to secure the boxes in the vehicle
- metaBOX 145 L empty, without inserts

Technical data

Characteristics

Dimensions	496 x 296 x 145 mm / 19.53 x 11.66 x 5.72 "
Case volume	14.1 l
Max. load cover	125 kg / 275.6 lbs
Weight	1.85 kg / 4.1 lbs
Material	ABS