

Connecting elements
H120,0/32

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For conductors from 10.0 to 185.0 mm² (AWG 7 - 350 MCM)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
• supplied loose in poly-bag

General ordering data

Type	H120,0/32
Order No.	9036240000
Version	Wire-end ferrule, uninsulated, 32 mm
GTIN (EAN)	4032248068036
Qty.	25 pc(s).
Packaging	loose

Creation date September 7, 2020 10:42:10 AM CEST

Catalogue status 05.09.2020 / We reserve the right to make technical changes.

Data sheet

Connecting elements H120,0/32

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 7.36 g

Technical data

Version uninsulated

Wire-end ferrules

Collar diameter (D2)	19 mm	Conductor cross-section	120 mm ²
Contact surface diameter (D1)	16.5 mm	L1 in mm	32 mm
Stripping length	32 mm	Wire connection cross section AWG, max.	AWG 4/0

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01
eClass 10.0	27-40-02-01	UNSPSC	31-16-31-02

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

Data sheet

Connecting elements
H120,0/32

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

