

TE Internal #: 1-1609965-2

3-Phase Filters, 6A 3-Phase Filter Current Rating, .250" FASTON

Input, .250" FASTON Output, DELTA (3 wire + ground)


View on TE.com >



EMI Filters > Power Line Filters > 3-Phase Filters











3-Phase Filter Current Rating: 6A

Input Type: .250" FASTON

3-Phase Filter Output Type: .250" FASTON
Wiring Configuration: DELTA (3 wire + ground)

3-Phase Filter Voltage (Max): 440 VAC

Features

Product Type Features

Filter Type	3-Phase Power Line
Filtered	Yes
Input Type	.250" FASTON
3-Phase Filter Output Type	.250" FASTON
Configuration Features	
Wiring Configuration	DELTA (3 wire + ground)
Electrical Characteristics	
Leakage Current (Max) (230VAC, 50Hz)	3
3-Phase Filter Current Rating	6 A
3-Phase Filter Current Rating 3-Phase Filter Voltage (Max)	6 A 440 VAC
3-Phase Filter Voltage (Max)	
3-Phase Filter Voltage (Max) Mechanical Attachment	440 VAC



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Customers Also Bought







TE Model / Part #2-644488-6

06P MTA100 SHRD HDR F/L R/A SN









TE Model / Part #7-2176316-2 MELF SMA_A 68K 1% 50PPM 0207 1W

=TE TE Model / Part #5-1437595-2 TRD11F10WL=SUB MINI ROCKER BLA

TE Model / Part #5-1879666-4 H8 475K 0.1% 15PPM







Documents

Product Drawings

KEB 6A 1S SPADE DELTA 440VAC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1609965-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1609965-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1609965-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use

Datasheets & Catalog Pages

6KEBS1AFPD

3-Phase Filters, 6A 3-Phase Filter Current Rating, .250" FASTON Input, .250" FASTON Output, DELTA (3 wire + ground)



KEB SERIES

English