

3KESS1BFPW ✓ ACTIVE


TE Internal #: 4-1609966-1

3-Phase Filters, 3A 3-Phase Filter Current Rating, .250" FASTON Input, .250" FASTON Output, WYE (4 wire + ground), 520VAC 3-Phase Filter Voltage (Max)

[View on TE.com >](#)



EMI Filters > Power Line Filters > 3-Phase Filters



3-Phase Filter Current Rating: **3 A**

Input Type: **.250" FASTON**

3-Phase Filter Output Type: **.250" FASTON**

Wiring Configuration: **WYE (4 wire + ground)**

3-Phase Filter Voltage (Max): **520 VAC**

Features

Product Type Features

Filter Type	3-Phase Power Line
Filtered	Yes
Input Type	.250" FASTON
3-Phase Filter Output Type	.250" FASTON

Configuration Features

Wiring Configuration	WYE (4 wire + ground)
----------------------	-----------------------

Electrical Characteristics

Leakage Current (Max) (230VAC, 50Hz)	3
3-Phase Filter Current Rating	3 A
3-Phase Filter Voltage (Max)	520 VAC

Mechanical Attachment

Mount Style	Flanged
-------------	---------

Usage Conditions

Operating Temperature Range	-25 – 85 °C
-----------------------------	-------------



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

[KES 3A 1S SPADE WYE 520VAC](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_4-1609966-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1609966-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1609966-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

3KES1BFPW

3-Phase Filters, 3A 3-Phase Filter Current Rating, .250" FASTON Input, .250" FASTON Output, WYE (4 wire + ground), 520VAC 3-Phase Filter Voltage (Max)



KES SERIES

English