

# EcoTank L3111



## DATASHEET / BROCHURE



Stylish and striking, this 3-in-1 inkjet is great for busy households looking to reduce their printing costs and enjoy mobile printing

Looking for a stylish and economical printer? This 3-in-1 EcoTank features a striking control panel and can reduce ink costs by 90% on average. With its enhanced ink filling system and new ink bottles engineered to minimise the risk of spills, this compact model proves a reliable and easy-to-use solution for printing in high volumes.

### Minimise refills with cartridge-free printing

While keeping on top of ink replacements is unlikely to be on anyone's priority list, running out of ink can be a massive hassle. EcoTank provides a stress-free solution - from the first set of inks its ultra-high capacity ink tanks can hold the equivalent of 88 cartridges' worth of ink<sup>1</sup> on average. It's great for those that print lots as it minimises changing supplies.

### Slash ink costs

This economical printer can save 90% on ink costs on average<sup>1</sup>. With one set of ink you can produce an impressive 4,500 pages in black and 7,500 in colour<sup>2</sup>.

### Specially engineered for ease of use

EcoTank is more compact and easier to use than ever before. Its front-facing tanks are engineered for mess-free refills and the bottles are designed to only allow the correct colours to be inserted. Thanks to the front ink level display, it's easy to see when it's finally due for a refill.

### Peace of mind

With a Micro Piezo printhead, EcoTank provides a reliable printing solution which is backed by a one year warranty

## KEY FEATURES

- **Save 90% on the cost of ink<sup>1</sup>**  
Equivalent of 88 cartridges' worth of ink included<sup>1</sup>
- **Ultra-low-cost printing**  
Print up to 4,500 pages in black and 7,500 pages in colour<sup>2</sup>
- **Next generation ink filling system**  
Enjoy hassle and mess-free refills with the enhanced ink bottles
- **3-in-1 with front loading tank**  
Print, copy & scan

## PRODUCT SPECIFICATIONS

### TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	3 pl, With Variable-Sized Droplet Technology
Ink Technology	Dye Ink
Printing Resolution	5,760 x 1,440 DPI
Nozzle Configuration	180 Nozzles Black, 59 Nozzles per Color
Category	Home, Home Office
All-in-One Functions	Print, Scan, Copy

### PRINT

Printing Speed ISO/IEC 24734	10 pages/min Monochrome, 5 pages/min Colour
Maximum Printing Speed	15 pages/min Colour (plain paper 75 g/m²), 33 pages/min Monochrome (plain paper 75 g/m²), 69 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper)

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

### SCAN

Optical Resolution	600 DPI x 1,200 DPI (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)
Single-sided scan speed (A4 black)	200 DPI; , 11 sec. with flatbed scan
Single-sided scan speed (A4 colour)	200 DPI; , 32 sec. with flatbed scan

### PAPER / MEDIA HANDLING

Number of paper trays	1
Paper Formats	C6 (Envelope), B5, A6, A5, A4, Legal, User defined, 13 x 18 cm, 10 x 15 cm, Letter, No. 10 (Envelope), DL (Envelope), 16:9
Duplex	Manual
Paper Tray Capacity	100 Sheets Standard, 100 Sheets Maximum, 20 Photo Sheets
Media Handling	Borderless print

### GENERAL

Energy Use	12 Watt (standalone copying, ISO/IEC 24712 pattern), 0.4 Watt (sleep mode), 3.9 Watt (Ready), 0.2 Watt (Power off)
Product dimensions	375 x 347 x 179 mm (Width x Depth x Height)
Product weight	3.9 kg
Noise Level	6.5 B (A) with Epson Premium Glossy Photo Paper / Photo RPM mode - 52 dB (A) with Epson Premium Glossy Photo Paper / Photo RPM mode
Compatible Operating Systems	Mac OS X 10.6.8 or later, Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Server 2008 R2, Windows Server 2012 R2, Windows Server 2016, Windows Vista, Windows XP SP3, Windows Server 2003 R2, XP Professional x64 Edition
Included Software	Epson Scan
Colour	Black

### OTHER

Warranty	12 months Carry in, 30,000 pages
----------	----------------------------------

## LOGISTICS INFORMATION

SKU	C11CG87404B2
EAN code	8715946690223
Country of Origin	Philippines

For more information please contact:

Home users: 0343 90 37766  
Business users\*: 0871 42 37766  
Republic of Ireland: 01 436 7742  
Or visit us at <https://www.epson.co.uk/contactus>  
\* 10p per minute plus network extras.

Web: [www.epson.co.uk](http://www.epson.co.uk)  
[www.epson.ie](http://www.epson.ie)


Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.  
Product information is subject to change without prior notice.  
Last extracted: 2020-08-19

## EcoTank L3111


### WHAT'S IN THE BOX

- Software (CD)
- Setup guide
- Power cable
- Main unit
- Warranty document
- 4 x 65ml individual ink bottles (Bk, C,Y,M)

### INK BOTTLE COMPATIBILITY

●	103	
●	103	
●	103	
●	103	

### INK BOTTLE YIELD DATA

		●	●	●
Included		3,600 pages*	6,500 pages*	
Replacement		4,500 pages*	7,500 pages*	

\* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. Average number of cartridges required /savings achieved printing the same number of pages using the ink bottles included within the EcoTank range, excluding hardware price. Comparison made on the average of the A4 EcoTank range versus the average of the top 10 best selling models in Western Europe, in the period January 2017– December 2017, as tracked by GfK. Printing costs calculated on the proportion of Standard and XL cartridges as tracked by GfK for the same reference period for the Western European market, using average retail prices. Ink cartridge yields as communicated by the manufacturer's websites.
2. Quoted yields are extrapolated based on Epson original methodology from the print simulation of Test Patterns provided in ISO/IEC 24712 based on the replacement ink bottles. Quoted yields are NOT based on ISO/IEC 24711. Quoted yields may vary depending on the images that you are printing, the paper type that you are using, the frequency of your prints and environmental conditions such as temperature. During the initial printer setup, a certain amount of ink is used to fill the print head's nozzles, therefore the yield of the initial bundled set can be lower.

**EPSON®**