



Anti-Corrosion

## RUST CONVERTER

### RESTORES CORRODED METAL

Rust Converter converts the rust formed from the oxidation of steel and iron into a paintable anti-corrosion layer. The cured coating is impermeable, tough and durable, preventing further corrosion. When dry, the dark grey coating acts as an effective primer for coloured top-coat application.

Totally free of lead and chromates, with no need for sand blasting, Rust Converter is fast acting: results visible in <5 minutes.

It's water based, with no chlorinated solvents and it can be finished with Galva Colour as top coat.

### PRODUCT CODES / FILL SIZES



30301 / 750ml

### APPLICATIONS

Suitable for use throughout the industry on: mechanical handling equipment, rolling stock, agricultural equipment, steel construction, ship repair, surface treatment, corrosion protection of all ferrous materials.

Rust Converter acts in three ways:

1. Inactivates existing rust: the unstable ferric hydroxide, formed at the start of the corrosion process of iron, is transformed into an inert complex, halting the corrosion process immediately.
2. Formation of a passivating protective coating: the formed complexes combine with the unique resin in Rust Converter creating a non-permeable coating, providing anti-corrosion protection.
3. Function as a primer: the cured dark grey, protective coating has an ideal structure and composition to act as a primer for future cosmetic over-painting.

### DIRECTIONS

- Stir or mix product before use.
- Stir frequently during application.
- Use only with adequate ventilation.
- Apply an even coat with a standard paint brush within a temperature range of 15 to 25°C. (dispose of brush, do not re-use).
- Allow Rust Converter to work – results will be visible in >5 minutes.
- Rust conversion at room temperature is approximately 30 minutes.
- Rust Converter will cure to a dry, dark grey finish – time dependent on application and rust.
- Leave for 24 hours before over-painting.

## TECHNICAL DATA (WITHOUT PROPELLANT)

Appearance	Viscous Liquid
Colour	Blue-green
Odour	Odourless
Density	1.2 g/cm <sup>3</sup> (@ 20°C)
pH	2.5-3.5
Flash Point	None
Rust Conversion Active Product	30 minutes
Rust Conversion Active Product	1 hour
Operational Temperature (Cured)	Maximum 60°C
Typical Coat Weight	20 µm
Coverage Per Litre	7m <sup>2</sup> /litre
Adhesion On Steel Dry Coating	0 GT
Salt Spray Resistance (ASTM B 117)	340 Hours at film thickness of 25 µm
Flexibility (Mandrel Test)	Pass : 7mm

## MATERIALS COMPATIBILITY

OK	-
CAUTION	-
NOT OK	-

## STORAGE & SHELF LIFE

The product should not be stored at temperatures below 5°C and do not mix with other products and has a shelf life of not less than 2 years with correct storage.

## HEALTH AND SAFETY

A separate Safety Data Sheet (SDS) according to EC Regulation 73/404/EEC and 648/2004/EC is available from Ambersil.com or via [info.uk@crcind.com](mailto:info.uk@crcind.com)

## MISREPRESENTATION ACT 1967

## TRADE DESCRIPTIONS ACT 1968

The information given in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which affect the use and performance of our products and for which reason no warranty is given, express or implied. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.

Version 3.1  
Created: July 2019  
Updated: October 2020

CRC Industries UK Ltd.  
Wylde Road, Bridgwater  
Somerset, TA6 4DD  
United Kingdom

t +44 (0)1278 727200  
f +44 (0)1278 425644  
e [sales.uk@crcind.com](mailto:sales.uk@crcind.com)  
w [www.ambersil.com](http://www.ambersil.com)

Company Registered No. 04910479

VAT No. GB 821 5195 42

