multicomp PRO

Wide input voltage non-isolated and regulated single output

RoHS Compliant



Description

MP-K78xx-1000R3 series are high efficiency switching regulators and ideal substitutes for LM78xx series three-terminal linear regulators. The converters feature high efficiency, low loss, short circuit protection, positive or negative output voltage, and there is no need for a heat sink. These product are widely used in applications such as industrial control, instrumentation and electric power.

c**¶**us C € CB

Features

- High efficiency up to 96%
- No-load input current as low as 0.1mA
- Operating ambient temperature range -40°C to +85°C
- · Support the negative output
- · Output short-circuit protection
- · Pin compatible with LM78xx series

	Input Voltage (VDC)*	Oı	utput	Full Load	Capacitive	
Part Number	Nominal (Range)	Voltage (VDC)	Current (mA) Max.	Efficiency (%) Vin Min. / Vin Max.	Load (µF) Max.	
MP-K7803-1000R3	24 (6-36)	3.3	1000	90/81	680	
MP-K7805-1000R3	24 (8-36)	5	1000	93/86		
MP-K/000-1000K3	12 (8-27)	-5	-500	86/82	330	
MP-K7809-1000R3	24 (13-36)	9	4000	95/90	680	
MD 1/7040 4000D0	24 (16-36)	12	1000	96/93	680	
MP-K7812-1000R3	12 (8-20)	-12	-300	89/88	330	
MD 1/7045 4000D2	24 (20-36)	15	1000	96/94	680	
MP-K7815-1000R3	12 (8-18)	-15	-300	89/89	330	

Input Specification	IS				
Item	Operating Conditions	Min.	Тур.	Max.	Unit
No-load Input Current	Positive output		0.1	1	mA
Input Filter			Capacita	nce filter	

1 For input voltage exceeding 30 VDC, an input capacitor of 22uF/50V is required.





Output Specifications						
Item	Operating Conditions			Тур.	Max.	Unit
Valtaria Angurani	Full load, input voltage range	MP-K7803-1000R3		±2	±4	
Voltage Accuracy		Others			±3	
Linear Regulation	Full load, input voltage range			±0.2	±0.4	%
Load Regulation	Nominal input , 10% -100% load			±0.4	±0.6	
Ripple & Noise*	20MHz bandwidth, nominal input, 20% -100% load			20	75	mVp-p
Temperature Coefficient	Operating temperature -40°C to +85°C		T		±0.03	%/°C
Transient Response Deviation	Nominal input, 25% load step change			50	300	mV
Transient Recovery Time				0.1	1	ms
Short-circuit Protection	Nominal input			ntinuous	, self-red	covery

Notes: * 1. The "parallel cable" method is used for Ripple and noise test, please refer to DC-DC Converter Application Notes for specific information;

^{2.} With light loads at or below 20%, Ripple & Noise for 3.3/5V output parts increases to 100mVp-p max, and for 9V/12V/15V output parts to 2%Vo max.

General Specifications						
Item	Operating Conditions			Тур.	Max.	Unit
Operating Temperature*	Derating if the temperature	Derating if the temperature ≥71°C (see Fig. 1)			85	°C
Storage Temperature					125	
Pin Soldering Resistance Temperature	Soldering time: 10 seconds				260	
Storage Humidity	Non-condensing	Non-condensing			95	%RH
Switching Frequency	Full load, nominal input	MP-K7803-1000R3/ MP-K7805-1000R3	420	520	620	KHz
		Other output	580	680	780	
MTBF	MIL-HDBK-217F@25°C		2000			K hours

Mechanical Specifications						
Case Material		Black plastic; flame-retardant and heat-resistant (UL94 V-0)				
Dimensions MP-K78xx-1000R3		11.5mm × 9mm × 17.5mm				
Weight		3.8g (Typ.)				
Cooling Method		Free air convection				

Electrom	Electromagnetic Compatibility (EMC)					
Emissions	CE	CISPR32/EN55032	CLASS B (see Fig. 4-2 for recommended circuit)			
EIIIISSIOIIS	RE	CISPR32/EN55032	CLASS B (see Fig. 4-2 for recommended circuit)			
	ESD	IEC/EN 61000-4-2	Contact ±4KV	perf. Criteria B		
	RS	IEC/EN 61000-4-3	10V/m	perf. Criteria A		
Immunity	EFT	IEC/EN 61000-4-4	±1KV (see Fig. 4-1 for recommended circuit)	perf. Criteria B		
	Surge	IEC/EN 61000-4-5	line to line ±1KV(see Fig. 4-1 for recommended circuit) perf. Criter			
	cs	IEC/EN 61000-4-6	3Vr.m.s	perf. Criteria A		



multicomp PRO

Typical Characteristic Curves








Fig. 1











multicomp PRO

Design Reference

1. Typical application



Positive output application circuit



Negative output application circuit




Fig. 3 Positive and Negative output application circuit

Table 1 C1/C3 C2/C4 Part Number (ceramic (ceramic capacitor) capacitor) MP-K7803-1000R3 22µF/10V MP-K7805-1000R3 MP-K7809-1000R3 10µF/50V 22µF/16V MP-K7812-1000R3 22µF/25V MP-K7815-1000R3

Note:

- 1. The required capacitors C1 and C2 (C3 and C4) must be connected as close as possible to the terminals of the module;
- 2. Refer to Table 1 for C1 and C2 (C3 and C4) capacitor values. For certain applications, increased values for C2 and C4 and/ or tantalum or low ESR electrolytic capacitors may also be used instead;
- 3. When using configurations as shown in figure 3, we recommended to add an inductor (LDM) with a value of up to 10μH which helps reducing mutual interference;
- 4. Converter cannot be used for hot swap and with output in parallel.

2. EMC compliance circuit




Fig. 4 EMC recommended circuit


FUSE	MOV	LDM1	C0	C1/C2	C5	LDM2
Select fuse value according to actual input current	S20K30	82µH	680µF /50V	Refer to table 1	4.7μF /50V	12µH


Note: Part 1 in Fig. 4 shows EMS compliance filter and part 2 filter for EMI compliance; depending on requirement both filters 1 and 2 can be used in series as shown.






Dimensions and Recommended Layout







Note: Grid 2.54*2.54mm

	Pin-Out					
Pin	+Output	-Output				
1	Vin	Vin				
2	GND	-Vo				
3	+Vo	GND				

Note: Unit:mm[inch] Pin diameter tolerances: $\pm 0.10[\pm 0.004]$ General tolerances: $\pm 0.25[\pm 0.010]$

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

