


Crimp Terminal Female

multicomp PRO



Specifications:

Max. Electric Current	:	AWG	22	20	18	16	14	12	10
	:	Amperes	3	4	7	10	15	20	24
Max. Electrical Rating	:	105°C 600V							
Insulation Material	:	Nylon							
Insulation Colour	:	Red (22AWG to 16 AWG)							
	:	Blue (16AWG to 14 AWG)							
	:	Yellow (12AWG to 10 AWG)							
Double Crimp	:	With copper sleeve on barrel							
Terminal Material	:	Brass							
Contact Plating	:	Tin							
Terminal Barrel ID	:	C : 1.7mm (22AWG to 16 AWG)							
	:	C : 2.3mm (16AWG to 14 AWG)							
	:	C : 3.4mm (12AWG to 10 AWG).							
Packing	:	100 pieces							
Connector Type	:	Disconnect							
Series	:	FDNYD							
Termination Type	:	Crimp							
Gender	:	Receptacle							

Specification Table

Wire Range AWG (mm ²)	Nema Tab	Dimensions Inches(mm)						Crimping Tool	Part Number
		W	F	L	B	D	T		
22 to 16 (0.5 to 1.5)	0.32 × 0.25 (0.8 × 6.35)	0.26 (6.6)	0.295 (7.5)	0.846 (21.5)	0.433 (11)	0.157 (4)	0.016 (0.4)	IZUMI Model 34 With Die Index Colour : Red or K.S. Model KST2000A With Die Index Colour : Red	FDNYD1-250
16 to 14 (1.5 to 2.5)						0.197 (5)			

Dimensions : Inches (Millimetres)

multicomp PRO

Crimp Terminal Female

multicomp PRO

Wire Range AWG (mm ²)	Nema Tab	Dimensions Inches(mm)						Crimping Tool	Part Number
		W	F	L	B	D	T		
12 to 10 (4 to 6)	0.32 × 0.25 (0.8 × 6.35)	0.26 (6.6)	0.295 (7.5)	0.925 (23.5)	0.512 (13)	0.256 (6.5)	0.016 (0.4)	IZUMI Model 5 With Die Index Colour : Yellow or K.S. Model KST2000A With Die Index Colour : Yellow	FDNYD5-250

Dimensions : Inches (Millimetres)

Part Number Table

Description	Part Number
Crimp Terminal, Female, Red , PK 100	FDNYD1-250
Crimp Terminal, Female, Blue , PK 100	FDNYD2-250
Crimp Terminal, Female, Yellow, PK 100	FDNYD5-250

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO