

08002

DEWALT®

DXV20P PROFESSIONAL WET & DRY VACUUM CLEANER

Rugged Quality Plastic Casing with hard wearing castors

Durable side catches & large sturdy On/OFF switch

Automatic ball-cock air shut-off

Blower Feature for removing dust & debris

Lightweight & portable

Powerful suction/blower motor

Hose & accessories supplied

20
LITRE

1050
W

48MM
HOSE
DIAMETER



DXV20P PROFESSIONAL WET & DRY VACUUM CLEANER

SPECIFICATIONS:

Input Supply	230 v 13 A
Power	1050 Watts
Mains Lead	3 m
Pressure	15 kPa (0,15 bar)
Air Flow	37,8 L/s
Tank Capacity	20 Litres
Hose	2,1 m x 48 mm
Net Weight	4,7 kG
Gross Weight	7,1 kG
Pack Dimensions	380 x 350 x 500 mm
Warranty	3 Year Limited

ACCESSORIES INCLUDED:



**DXVC4001
CARTRIDGE FILTER**



**DXVA19-1400
CREVICE NOZZLE**



**DXVA19-1900D
FLOOR NOZZLE**



**DXVA19-1300
UTILITY NOZZLE**



**DXVA25-4204
DISPOSABLE DUST BAG**



**DXVA19-1202
EXTENSION WAND**



**DXVA19-2558
HOSE**



**DXVA19-5158
HOLDER/BAG**

GUARANTEED TOUGH®

Online Customer Service Centre at: www.2helpU.com

DEWALT®