

750W, 18 to 60V Input Non-Isolated Step Down DC-DC Converter

<https://product.tdk.com/en/power/i7a>
www.emea.lambda.tdk.com/i7a



Industrial



Test



COMM



Broadcast



The i7A series of up to 750W non-isolated DC-DC step-down converters are ideal for creating additional high current/high power 33A and 45A output voltage rails from a single output 24V, 36V or 48V AC-DC or DC-DC power supply. The highly efficient i7A series has low ripple, excellent dynamic response under sudden load changes, accepts a wide DC input with a wide output adjustment range. Three mechanical configurations are available; low profile open frame, baseplate construction for conduction cooling, or models with an integral heat sink for convection or forced air cooling. The i7A series expands upon TDK-Lambda's existing 100 to 250W rated i3A/i6A series and reduces the need to parallel modules.

Features	Benefits
• Up to 750W in a 1/16th Brick Footprint	• High Power Density, Less Board Area Needed
• High Efficiency - Up to 98.5%	• Longer Battery Life / Less Power Consumed
• Wide 3.3 to 18V or 3.3 to 24V Output Adjustment	• One Part Supports Multiple System Voltages
• 18 to 32V or 18 to 60V Input Ranges	• Can Operate From Different DC Source Voltages Including Batteries
• Low Component Count With Minimal External Components	• Low Cost
• Minimal Derating Requirements in Low Airflow Environments	• Easy To Cool In End System

Model Selector								
Model	Input Voltage (V)	Output Voltage (V)	Max Current (A)	Max Power (W)	Positive Logic On/Off	Negative Logic On/Off	Integrated Baseplate	Integrated Heatsink
i7A4W033A033V-000-R	18 - 60	3.3 - 24	33	500	Yes	-	-	-
i7A4W033A033V-001-R	18 - 60	3.3 - 24	33	500	-	Yes	-	-
i7A4W033A033V-0C1-R	18 - 60	3.3 - 24	33	500	-	Yes	Yes	-
i7A4W033A033V-0F1-R	18 - 60	3.3 - 24	33	500	-	Yes	-	Yes
i7A24045A033V-000-R	18 - 32	3.3 - 18	45	750	Yes	-	-	-
i7A24045A033V-001-R	18 - 32	3.3 - 18	45	750	-	Yes	-	-
i7A24045A033V-0C1-R	18 - 32	3.3 - 18	45	750	-	Yes	Yes	-
i7A24045A033V-0F1-R	18 - 32	3.3 - 18	45	750	-	Yes	-	Yes

Consult sales for release dates.


Related Products		
Type	Part Number	Description
Evaluation Kit	i7A33A-C01-EVK-S1	Evaluation board with i7A4W033A033V-001-R module.
	i7A45A-C01-EVK-S1	Evaluation board with i7A24045A033V-001-R module.

Specification			
Model		i7A4W033A033V	i7A24045A033V
Input			
Input Voltage Range	Vdc	18-60 (Turn on at 16.5 typ)	18-32 (Turn on at 16.5 typ)
Input Transient (t < 100 ms)	Vdc	65 max	36 max
Input Current (max)	A	50	
Efficiency	%	91 - 98	93 - 98.5
Safety Agency Certifications	-	IEC/EN/UL/CSA 62368-1, CE Mark	
Output			
Output Voltage Tolerance	%	±3.5	
Switching Frequency	kHz	660	
Line Regulation	%	0.2	
Load Regulation	%	0.4	
External Load Capacitance	uF	220 - 10000	330 - 10000
Output Current	A	0 - 33	0 - 45
Ripple & Noise	mV	25	
Overcurrent Protection Threshold (typ)	A	45	63
Overtemperature Protection	-	Yes	
Remote Sense	-	(+) Sense, compensating up to 5% of output voltage	
Remote On/Off	-	See Model Selector table (Negative Logic: Von/off < 0.25V @ 1mA sink; Module = On)	
Output Adjust	-	See detailed specifications for trim equation.	
Dynamic Response	-	420 mV / 70 µs typ @ Vo=12V, 1 A/µs, 25% to 75% Step Load)	
Environmental			
Operating Temperature (Tref)	°C	-40 to 125 (see thermal data on website)	
Storage Temperature	°C	-55° to +125	
Humidity (non condensing)	%RH	5 - 95%RH (Operating & Storage)	
Cooling	-	Convection, conduction (baseplate) or forced air	
Random Vibration (Operating)		IEC 60068-2-64 / IPC9592B: 2.40 Grms, 10-500 Hz, 30 min per x, y, z axis	
Shock (Operating)		IEC 60068-2-27 / IPC9592B: 30G, 11ms per x, y, z axis	
Other			
Weight (Typ)	g	Open Frame: 25g, with Baseplate: 50g, with Heatsink: 70g	
Size (LxWxH)	mm	Open Frame: 34 x 36.8 x 11.5	
		With Baseplate: 34 x 36.8 x 12.7	
		With Heatsink: 34 x 36.8 x 24.9	
Size (LxWxH)	Inches	Open Frame: 1.34 x 1.45 x 0.45	
		With Baseplate: 1.34 x 1.45 x 0.50	
		With Heatsink: 1.34 x 1.45 x 0.98	
MTBF - Telcordia SR-332	-	> 5 Mhrs; 100% Load; Ta = 40 °C	
Warranty	yrs	3 years	


Notes

See website for detailed [specifications](#) and test methods.


Typical Application Circuit



i7A4W033A033V: Output vs. Input Voltage Operating Range




i7A24045A033V: Output vs. Input Voltage Operating Range




Mechanical Specification


Outline Drawing Open frame –00x-R product options



Outline Drawing With Baseplate –xCx-R product options




Outline Drawing With Heatsink –xFx-R product options




Mechanical Specification

Recommended Hole Pattern – i7A4W033A033V-xxx-R (Top View)



Recommended Hole Pattern – i7A24045A033V-xxx-R (Top View)



Pinout

PIN	Function	PIN	Function
1	VIN (+)	6	TRIM
2	ON / OFF	7	SENSE (+)
3	VIN (-) / GND	8	VOUT (+)
4	VOUT (-) / GND	9*	VIN (+)
5	Not Populated	10*	VIN (-) / GND

* Pin 9 & 10 are added for products drawing higher input currents (e.g. i7A24045A033V-xxx-R)
Pin base material is brass or copper with gold over nickel plating.

