
High Quality Power Cord UL Certificated

multicomp PRO

E345335, 10A 125V-



RoHS **Compliant**



2000±76.2 (78.74"±3")




ME-301 (NEMA 5-15P) (Dimensions of Plug Face)



SJT 18AWGx3c (Wire Cross-Section)

PVC Insulation Thickness 0.76(>0.69mm) Overall Diameter 2.75±0.10mm Copper Conductor 41/0.160±0.003mm Diameter 1.18mm (Approx.)

> PVC Jacket Thickness 0.76mm(>0.61mm) Overall Diameter 7.8±0.2mm



ME-302 (IEC 60320, C13, 10A 125V~) (Dimensions of Connector Face)

Dimensions: Millimetres

Plug Component			
Colour Component		Qty	
35P (Black)	ME-301 (Nema 5-15P)	1	
Nickel-plated	4.75 GEM 98475ABS-1 (#14-#18) (Earth Pins Terminal)	1	
Nickel-plated	6.3×15 (#16-18) GEM 98675BBS-1 (Solid Blades)	2	
Black	301-1 (5-15P Inner Body)	1	

	Strip	ROJ	Colour
	6 +1/-0	22 ±2	Brown (L)
	6 +1/-0	22 ±2	Blue (N)
	6 +1/-0	22 ±2	Green-Yellow (E)

Wire Styles
SJT18AWGx3C
(CEE Cord)
60°C Black
Length: 2,000mm ±76.2mm
78.74" ±3"

Connector Component			
Instruction	Qty.	Colour	
ME-302 (IEC 60320, C13, 10A, 125V)	1	35p (Black)	
2.0 × 4.0 GEM 98740BS-0 (#16-18) Receptacle Terminal	3	Brass-Natural	
GA005-5 (2.0 × 4.0 Serial Housing)	1	Off-White	

Dimensions				
ROJ	Strip	Colour		
16±1	5 +1/-0	Brown (L)		
16±1	5 +1/-0	Blue (N)		
16±1	5 +1/-0	Green-Yellow (E)		

Dimension

Dimensions: Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



High Quality Power Cord UL Certificated



Note:

1. Hi-Pot Test: 1,500V/1Sec; <0.5mA

2. Insulation Resistance Test : DC 500/min>100m Ω

- 3. Continuity & Polarization Test: No short circuit, break circuit, displacement.
- 4. Each end terminal shall be capable of withstanding a pull of 25lbs for 1 minutes without loosening.
- 5. Strain relief shall be capable of withstanding a pull of 35lbs for 1 minutes without loosening.
- 6. All material according to Non-toxic standard.

Part Number Table

Description	Part Number
5-15P to C13, SJT, CEE, 18/3C,10A 125V	MC-156

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

