Note: This datasheet may be out of date.

Please download the latest datasheet of KRM55LR72A475KH01# from the official website of Murata Manufacturing Co., Ltd.

"#" indicates a package specification code.

http://www.murata.com/en/products/productdetail?partno=KRM55LR72A475KH01%23

http://www.murata.com/en/products/productdetail?partito=KKNISSEK72A475KH017625





















< List of part numbers with package codes > KRM55LR72A475KH01K KRM55LR72A475KH01L



Appearance & Shape







Packaging	Specifications	Minimum Order
		Quantity
К	330Embossed Tape	2000
L	180Embossed Tape	400

Mass (typ.)	
1 piece	0.32g

1 of 4

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



KRM55LR72A475KH01#

Note: This datasheet may be out of date.

 $Please\ download\ the\ latest\ data sheet\ of\ KRM55LR72A475KH01\#\ from\ the\ official\ website\ of\ Murata$ Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=KRM55LR72A475KH01%23

"#" indicates a package specification code.



Specifications

Length	6.1±0.4mm
Width	5.3±0.2mm
Thickness	2.8±0.2mm
Capacitance	4.7μF ±10%
Metal terminal width e	1.2±0.2mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	100Vdc
Capacitance change rate	±15%
Temperature characteristics (complied standard)	X7R(EIA)
Temperature range of temperature characteristics	-55°C to 125°C

2 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Note: This datasheet may be out of date. Please download the latest datasheet of KRM55LR72A475KH01# from the official website of Murata Manufacturing Co., Ltd.


"#" indicates a package specification code.




Characteristic Data


KRM55LR72A475KH01#


The charts below may show another part number which shares its characteristics.














KRM55LR72A475KH01 C-AC Voltage capchange, DCOV, 25.0d

3 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




Please download the latest datasheet of KRM55LR72A475KH01# from the official website of Murata Manufacturing Co., Ltd.


http://www.murata.com/en/products/productdetail?partno=KRM55LR72A475KH01%23

Note: This datasheet may be out of date.

"#" indicates a package specification code.

KRM55LR72A475KH01#





4 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

