


Datasheet

RTD Extension Cable – 4 core PFA

Platinum Resistance Thermometer Extension Cable, PFA insulated & screened



- PFA insulated cable for extending Platinum Resistance Thermometers
- High temperature to 260°C, extruded PFA Teflon® construction
- Commonly used for Pt100Ω thermometers, also suitable with other types such as Pt130, Pt500 & Pt1000Ω
- Construction – PFA insulated 7/0.2mm tin plated copper conductors, twisted cores with nylon cord, tin plated copper braided screen with PFA insulated outer jacket
- Cores colour coded Red & White in accordance with IEC-751, black outer jacket
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Insulation rating -75°C to 260°C

Type	Conductors	mm ²	Cores	Screen	Jacket	Reel Length	Manufacturers Code	Order Code
RTD	7/0.2mm	0.219	x 4	Yes	Black	5 metres	WC-052-D	XF-1588-FAR
RTD	7/0.2mm	0.219	x 4	Yes	Black	10 metres	WC-052-D	XF-522-FAR
RTD	7/0.2mm	0.219	x 4	Yes	Black	25 metres	WC-052-D	XF-1328-FAR
RTD	7/0.2mm	0.219	x 4	Yes	Black	50 metres	WC-052-D	XF-1327-FAR
RTD	7/0.2mm	0.219	x 4	Yes	Black	100 metres	WC-052-D	XF-1326-FAR

Overall sheath Dimension (approx.)

4 core: 3.2mmØ