




ELECTRICAL TEST:

1. 100% OPEN SHORT MIS WIRE TEST
2. CONTACT RESISTANCE: 3 OHM MAX
3. INSULATION RESISTANCE: 5M OHM MIN
4. HI-POT TEST: DC 300V/10ms
5. PASS 3840 * 2160P @ 30HZ / TEST


CONSUMER ITEM	LENGTH(mm)
PSG3404-30HZ-1M	1000±30
PSG3405-30HZ-2M	2000±30
PSG3406-30HZ-3M	3000±30

USB 3.1 CM

HDMI A/M



★HDMI A/M 2171



NO.	PART NAME	DESCRIPTION	UNIT
⑦	Cable	USB3.1 (#32*1P+D+AL+HM)*4C+#32*4C+#32*1P+#24*1C+#26*1C+AB+BC Braid PVC BLACK Jacket OD4.7MM	M
⑥	outer molding	BLACK PVC 45P	20g
⑤	inner molding	PE, Nature color	10g
④	SHELL	BLACK ABS SHELL L45*W21.2mm	1PCS
③	SHELL	BLACK ABS SHELL L21*W12.25mm	1PCS
②	Connector	HDMI AM 19P PIN:G/F,SHELL:Gold plated	1PCS
①	Connector	USB C/M PIN:G/F,SHELL:Gold plated	1PCS

FARREACH			
DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT
MODEL NO.	TP-C021A	△	
APPROVED	CHECKED	DRAWING	DESIGNED
		YAN	YAN
DRAWING NO.	256-053	FINISHING	MATERIAL
		△	
		2020/11/05	
		SYM	DATE
			REVISION