



## Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 7

TEROSON VR 5080 known as Fix'n'Repair Tape 25m,Scandi

SDS No. : 200194  
V002.4

Revision: 22.05.2015  
printing date: 26.11.2020

Replaces version from: 09.09.2014

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

TEROSON VR 5080 known as Fix'n'Repair Tape 25m,Scandi

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Pressure-sensitive adhesive

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.2. Label elements

##### Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.3. Other hazards

None if used properly.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

##### General chemical description:

Pressure sensitive tape

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Contains no dangerous substances exceeding the limits of the EU-Regulation

**SECTION 4: First aid measures**

**4.1. Description of first aid measures**

**Inhalation:**

Not applicable; the product cannot be inhaled.

**Skin contact:**

Rinse with running water and soap.  
Seek medical advice.

**Eye contact:**

In case of adverse health effects seek medical advice.

**Ingestion:**

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.  
Seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

**4.3. Indication of any immediate medical attention and special treatment needed**

See section: Description of first aid measures

**SECTION 5: Firefighting measures**

**5.1. Extinguishing media**

**Suitable extinguishing media:**

Carbon dioxide, foam, powder

**Extinguishing media which must not be used for safety reasons:**

None known

**5.2. Special hazards arising from the substance or mixture**

In case of fire, keep containers cool with water spray.  
carbon oxides.

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

**SECTION 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid skin and eye contact.

**6.2. Environmental precautions**

Do not let product enter drains.

**6.3. Methods and material for containment and cleaning up**

Scrape up as much material as possible.  
Keep in suitable and closed containers for disposal.

**6.4. Reference to other sections**

See advice in section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Use only in well-ventilated areas.  
Avoid skin and eye contact.  
See advice in section 8

#### Hygiene measures:

Good industrial hygiene practices should be observed.  
Wash hands before work breaks and after finishing work.  
Do not eat, drink or smoke while working.

### 7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

### 7.3. Specific end use(s)

Pressure-sensitive adhesive

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational Exposure Limits

Valid for  
Great Britain

None

#### Biological Exposure Indices:

None

### 8.2. Exposure controls:

#### Respiratory protection:

Use only in well-ventilated areas.

#### Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq$  0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq$  0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

#### Eye protection:

Wear protective glasses.

#### Skin protection:

Wear suitable protective clothing.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	Tape Tape silver
Odor	characteristic
Odour threshold	No data available / Not applicable
pH	Not available.
Initial boiling point	Not available.
Flash point	Not applicable
Decomposition temperature	No data available / Not applicable
Vapour pressure	Not applicable
Density	0,93 g/cm <sup>3</sup>
( )	
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Insoluble
(Solvent: Water)	
Solubility (qualitative)	Insoluble
(Solvent: Acetone)	
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

**SECTION 10: Stability and reactivity****10.1. Reactivity**

Strong oxidizing agents.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

Stable under normal conditions of storage and use.

**10.5. Incompatible materials**

See section reactivity

**10.6. Hazardous decomposition products**

carbon oxides.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

#### General toxicological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

#### Oral toxicity:

This material is considered to have low toxicity if swallowed.

#### Inhalative toxicity:

Due to the low volatility of the product there are no hazards associated with inhalation under normal conditions of use

#### Skin irritation:

Prolonged or repeated contact may cause skin irritation.

#### Eye irritation:

Prolonged or repeated contact may cause eye irritation.

## SECTION 12: Ecological information

#### General ecological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

### 12.1. Toxicity

#### Ecotoxicity:

Do not empty into drains / surface water / ground water.

### 12.2. Persistence and degradability

No data available.

### 12.3. Bioaccumulative potential / 12.4. Mobility in soil

No data available.

### 12.5. Results of PBT and vPvB assessment

No data available.

### 12.6. Other adverse effects

No data available.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product disposal:**

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

**Disposal of uncleaned packages:**

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

**Waste code**

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

**SECTION 14: Transport information****14.1. UN number**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

**14.2. UN proper shipping name**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

**14.3. Transport hazard class(es)**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

**14.4. Packaging group**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

**14.5. Environmental hazards**

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

**14.6. Special precautions for user**

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

**14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**

not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content 0 %  
(1999/13/EC)

### 15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

## SECTION 16: Other information

### Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**