

Safety isolating transformer AVB 1,5/2/15



Picture shows AVB 3,2/2/18

Advantages

Minimum size at high output
Inherently short-circuit proof
Dual input voltage for series or parallel connection
Also with dual output voltage for series or parallel connection
Designed for high ambient temperatures
Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDenseFill resin encapsulation
Self-extinguishing potting and hood material

Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As a safety transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

Sample application



Standards

Safety isolating transformer
to: VDE 0570 Part 2-6, DIN EN 61558-2-6, EN 61558-2-6, IEC 61558-2-6,
UL 5085-1/-2, CSA 22.2 No.66

Approvals




UL 5085-1/-2, CSA 22.2 No.66



Safety isolating transformer AVB 1,5/2/15

Electrical data		Type	AVB 1,5/2/15
Input			
Rated input voltage			2 x 115 Vac
Rated frequency			50 - 60 Hz
Output			
Rated output voltage			2 x 15 Vac
Rated Power			1.5 VA
No-load voltage (app. x factor)			1.39
No-load loss (typ.)			1.00 W
Efficiency			57.0 %
Standards			
Classification			Safety isolating transformer
Approvals			
Approvals			cURus
Environment			
Ambient temperature max.			70 °C
Safety and protection			
Type			Encapsulated
Insulation class			VDE=B, UL=class 105
Protection index			IP 00
Safety class (prepared)			II
Short circuit strength			inherently short-circuit proof
Order numbers			
Order Number			AVB 1,5/2/15

Mechanical data		Type	AVB 1,5/2/15
Terminal and mounting			
Terminals			Pins for printed circuit boards
Pin (ø)			0.8
Measures and weights			
Core type			EI 30/12,5
Weight			0.08 kg



Subject to change.