

**Test Report**

No. 2077320/EC

Date : Oct 09 2006

Page 1 of 3

PRO-POWER PRODUCTS MANUFACTURED BY
KAI SUH SUH ENTERPRISE CO LTD
38, YEN PING N. ROAD, SEC.1, TAIPEI, TAIWAN, R.O.C.

This report is to supersede test report number 2063110/EC.

Report on the submitted sample said to be NYLON CABLE GLAND (BLACK COLOR).

SGS Job No. : 1018475
Buyer : PREMIER FARNELL ASIA PTE LTD
Supplier Part No. : AG SERIES
Country of Origin : TAIWAN
Sample Receiving Date : JUN 09 2006
Testing Period : JUN 09-13 2006

Test Requested : With reference to RoHS Directive 2002/95/EC

- 1) To determine the Cadmium Content in the submitted sample.
- 2) To determine the Lead Content in the submitted sample.
- 3) To determine the Mercury Content in the submitted sample.
- 4) To determine the Hexavalent Chromium Content on the submitted sample.
- 5) Determination of PBBs (polybrominated biphenyls), PBDEs (Polybrominated diphenylethers) of the submitted sample.

Test Method :

- 1) With reference to BS EN 1122:2001, Method B, analysis was performed by Inductively Coupled Argon Plasma-Atomic Emission Spectrometry (ICP-AES).
- 2) With reference to EPA Method 3050B/ 3051/ 3052. Analysis was performed by Inductively Coupled Argon Plasma-Atomic Emission Spectrometry (ICP-AES).
- 3) With reference to EPA Method 3051/ 3052. Analysis was performed by Inductively Coupled Argon Plasma-Atomic Emission Spectrometry (ICP-AES).
- 4) With reference to EPA Method 3060A & 7196A. The sample was alkaline digested by using EPA Method 3060A, and then analyzed by using Colorimetric method 7196A (by UV-Vis Spectrophotometer).
- 5) With reference to EPA Method 3540C/ 3550C. Analysis was performed by GC/MS or LC/ MS.

Test Results : 1-5) Please refer to next page.

Conclusion : When tested as specified, the submitted sample complies with the requirements of Commission Decision of 18 Aug 2005 amending Directive 2002/95/EC notified under document 2005/618/EC.

Signed for and on behalf of
SGS Hong Kong Ltd

Ho Ka Ting, Family
Senior Laboratory Executive

This document is issued by the Company subject to its General Conditions of Service printed overleaf or available on request and accessible at www.sgs.com. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. Unless otherwise stated: (a) the results shown in this document refer only to the sample(s) tested and (b) such sample(s) are retained for 30 days only. This document cannot be reproduced except in full, without prior approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this report is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Hong Kong Ltd. 5/F - 8/F, 12/F & 28/F - 29/F, Metropole Square, 2 On Yiu Street, Siu Lek Yuen, Shatin, N.T., Hong Kong. t (852) 2334 4481 f (852) 2764 3126 www.hk.sgs.com

H 13917205



Test Report

No. 2077320/EC

Date : Oct 09 2006

Page 2 of 3

Test Results

1-4)

Test Item	1	2	3	Detection Limit	Limit
Cadmium (Cd)	ND	ND	ND	2 ppm	100 ppm
Lead (Pb)	ND	ND	ND	2 ppm	1000 ppm
Mercury (Hg)	ND	ND	ND	2 ppm	1000 ppm
Hexavalent Chromium (Cr ⁶⁺)	ND	ND	ND	2 ppm	1000 ppm

(Results shown are of the total weight of samples)

Note : ppm = mg/kg

ND = Not Detected

Not detected is reported when the reading is less than detection limit value

5)

Flame Retardants	1	2	3	Detection Limit	Limit
Polybrominated Biphenyls (Mono – Deca)	ND	ND	ND	50 ppm	1000 ppm
Monobromobiphenyl	ND	ND	ND	5 ppm	--
Dibromobiphenyl	ND	ND	ND	5 ppm	--
Tribromobiphenyl	ND	ND	ND	5 ppm	--
Tetrabromobiphenyl	ND	ND	ND	5 ppm	--
Pentabromobiphenyl	ND	ND	ND	5 ppm	--
Hexabromobiphenyl	ND	ND	ND	5 ppm	--
Heptabromobiphenyl	ND	ND	ND	5 ppm	--
Octabromobiphenyl	ND	ND	ND	5 ppm	--
Nonabromobiphenyl	ND	ND	ND	5 ppm	--
Decabromobiphenyl	ND	ND	ND	5 ppm	--
Polybrominated Diphenylethers (Mono – Nona)	ND	ND	ND	45 ppm	1000 ppm
Monobromodiphenyl ether	ND	ND	ND	5 ppm	--
Dibromodiphenyl ether	ND	ND	ND	5 ppm	--
Tribromodiphenyl ether	ND	ND	ND	5 ppm	--
Tetrabromodiphenyl ether	ND	ND	ND	5 ppm	--
Pentabromodiphenyl ether	ND	ND	ND	5 ppm	--
Hexabromodiphenyl ether	ND	ND	ND	5 ppm	--
Heptabromodiphenyl ether	ND	ND	ND	5 ppm	--
Octabromodiphenyl ether	ND	ND	ND	5 ppm	--
Nonabromodiphenyl ether	ND	ND	ND	5 ppm	--
Decabromodiphenyl ether*	ND	ND	ND	5 ppm	See remark

Note : ppm = mg/kg

ND = Not Detected

Not detected is reported when the reading is less than detection limit value.

Remark: * Decabromodiphenyl ether (DecaBDE) in polymeric applications is exempted by Commission Decision of 13 Oct 2005 amending Directive 2002/95/EC notified under document 2005/717/EC.

Sample Description :

1. Black Plastic (Ring , Body & Cap)
2. Black Rubber (Ring Inside)
3. Black Rubber (Ring)

SGS

Test Report

No. 2077320/EC

Date : Oct 09 2006

Page 3 of 3

PHOTO APPENDIX



SGS authenticate the photo on original report only

*** End of Report ***

This document is issued by the Company subject to its General Conditions of Service printed overleaf or available on request and accessible at www.sgs.com. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. Unless otherwise stated: (a) the results shown in this document refer only to the sample(s) tested and (b) such sample(s) are retained for 30 days only. This document cannot be reproduced except in full, without prior approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this report is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Hong Kong Ltd 5/F - 8/F, 12/F & 28/F, Metropole Square, 2 On Yiu Street, Siu Lek Yuen, Shatin, N.T., Hong Kong. t (852) 2334 4481 f (852) 2764 3126 www.hk.sgs.com

H13917207

Member of the SGS Group (SGS SA)