

Quickset Adjustable Torque Screwdrivers

Torque range from 0.2 to 9 N.m


Quickset Adjustable Torque Screwdrivers are calibrated scale tools that can be used for the accurate and consistent application of torque in any manufacturing, engineering or servicing environment. Their adjustability and wide range of torque make them suitable for a broad range of applications. These tools are durable, easy to use and the unique Slipping Technology means that the risk of over or under tightening is eliminated.



Quickset 6 FH

T-Bar is not included with the Ergo Quickset Screwdriver Range

Slipping Mechanism
Incorrect tightening is impossible



INDUSTRY SECTORS

Maintenance & Repair



Quickset Adjustable Torque Screwdrivers (ISO and Imperial Scales)

Absolute accuracy and consistency. Accurate process control is ensured by eliminating under and over tightening due to the unique Slipping Technology

Calibrated scale. A visible scale allows the user to adjust the tool to their desired torque setting, enabling a range of different torque settings to be applied

Ease of use. Tools can be used with confidence by operators at any skill level, due to unique slipping mechanism

Easy to set up. Fast and accurate to set, using the quick and clear to read micrometer style setting scale

Improved production quality. Accurate torque application reduces the likelihood of warranty and rework

Increased production efficiency. Increased operator comfort and productivity, from the smooth reset action of the tool and the ergonomic design

Long tool life. High quality, robust construction. Many years of dependable service are provided by the robust design and hard-wearing materials, that include stainless steel and aluminium

Operational versatility. These versatile tools are ideal for a wide range of applications, due to their adjustability and wide torque range



Additional features

Accessories. **See pages 84-95**

EPA compliant alternative available. **See page 32**

Optional Lock On T-Bar for larger models of screwdriver, provides extra leverage when required. (Order Code: P29530)

Tool can be kept accurate and up to date with our Calibration service. **See page 98 for details**

For more information: Tool Selector; gedore-torque.com/tool-selector Telephone; +44 (0) 1483 894 476
Videos; www.youtube.com/gedore-torque Email; salesandrepairs@gedore-torque.com

Want to know how to use this tool?



Watch our video

Order Code	Model	← Calibrated Range →		Drive	k mm	g	Repeatability	ISO 6789 Class	Colour
		Range	سسسس						
016040	Quickset Minor Metric FH	20-120 cN.m	1 cN.m	1/4"	169	165	+/- 6%	2D	Blue
016060	Quickset Minor Imp FH	20-120 ozf.in	1 ozf.in	1/4"	169	165	+/- 6%	2D	Blue
016070	Quickset Minor lbf.in FH	2-12 lbf.in	0.1 lbf.in	1/4"	169	165	+/- 6%	2D	Blue
016500	Quickset 6 FH	1-6 N.m	0.1 N.m	1/4"	184	335	+/- 6%	2D	Blue
016600	Quickset 50 FH	5-50 lbf.in	1 lbf.in	1/4"	184	335	+/- 6%	2D	Blue
016700	Quickset 9 FH	4-9 N.m	0.1 N.m	1/4"	184	335	+/- 6%	2D	Blue
016800	Quickset 80 FH	30-80 lbf.in	1 lbf.in	1/4"	184	335	+/- 6%	2D	Blue

Dual Scale Quickset Screwdrivers Available:

Order Code	Model	← Calibrated Range →			Drive	k mm	g	Repeatability	ISO 6789 Class	Colour
		ISO	سسسس	Imperial						
016011	Quickset Minor DS	20-120 cN.m	1 cN.m	20-120 ozf.in	1 ozf.in	160	158	+/- 6%	2D	Blue
016550	Quickset 6 DS	1-6 N.m	0.1 N.m	5-50 lbf.in	1 lbf.in	169	340	+/- 6%	2D	Blue