

Multi-Purpose Grease

Product Code: MPG

PRODUCT DESCRIPTION

This general purpose grease, supplied in tubes, is for use in many mechanical and electrical applications.

PRODUCT USE

Most mechanical and electrical applications where good lubrication and thermal properties are required.

FEATURES

- * Wide temperature range.
- * Good lubricating and thermal properties.
- * Safe on most thermoplastics.
- * Conveniently packed in 50ml tubes.

TYPICAL PROPERTIES

Form:	Light Brown Grease
Viscosity (Base Oil, 40°C):	463 cSt
Flash Point:	230°C
Pour Point:	-11°C
Drop Point:	>250°C
Temperature Range:	-20°C to +200°C
Penetration (Unworked):	260-290

DIRECTIONS FOR USE

Apply to both surfaces sparingly.

TECHNICAL
DATA
SHEET



**Copyright
Electrolube
2003**

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.



Multi-Purpose Grease – Page 2

PACKAGING

50ml Tube

ORDER CODE

MPG50T

NATO Stock no: 9150-99-660-1415

TECHNICAL
DATA
SHEET



Copyright Electrolube 2003

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

