

# Heat Shrinkable Polyolefin Tubing



## Features

- Excellent mechanical strength
- Abrasion resistance
- Excellent optical clarity
- Environmental sealing
- Shrink ratio 4:1
- Length: 1.22m (4ft)

**RoHS  
Compliant**

## Applications

The product is a flexible, heat shrinkable, dual wall tubing with an integrally bonded meltable adhesive inner liner designed to offer moisture proof encapsulation to a wide variety of substrates. In particular, it adheres well to PVC.

Available in clear, the product offers excellent clarity for protection of substrates that may need to be inspected during service. The tough outer jacket gives excellent mechanical strength with a high resistance to splitting. The highshrink - ratio means that only four sizes are needed to give protection to a full range of irregular shapes with widely varying dimensions.

## Temperature Range

### Installation

- Min. Shrink Temperature : 60°C (140°F)  
 Min. Full Recovery Temperature : 100°C (212°F)  
 Operating Temperature : -55°C to 75°C (-67°F to 167°F)

## Product Dimensions

Size	Inside Diameter		Recovered Wall Thickness*	
	Min. Expanded as Supplied	Max. Recovered After Heating	Nominal Total Wall After Heating	Nominal Adhesive Wall After Heating
16/4	16 (0.63)	4 (0.158)	1.5 (0.059)	0.5 (0.02)

\*Wall thickness will be less if tubing recovery is restricted during shrinkage.

Dimensions : Millimetres (Inches)

## Part Number Table

Description	Part Number
Heat Shrink Tubing, Transparent, 1.22m	DWFC-16/4-X-STK

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands  
 Farnell.com/exclusive-brands  
 Element14.com/exclusive-brands

