

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2162701041

Status:


Active

Overview:

Off-the-Shelf Cable Assemblies

Description:

SL Female-to-SL Female Off-the-Shelf (OTS) Cable Assembly, Positive Lock, Single Row, 100.00mm Length, Tin (Sn) Plating, 4 Circuits, Black



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Cable Assemblies
Series	216270
Application	Signal, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	SL-to-SL
Overview	Off-the-Shelf Cable Assemblies
Product Name	SL
Type	Discrete Wire Assembly
UPC	193264730650
Physical	
Cable Length	100.00mm
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	3.609/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.63mm max.
Wire Size AWG	22
Wire/Cable Type	UL 11028
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	600V AC/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2162701040-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
Terphenyl,
hydrogenated
2-(2H-benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
2-(2H-benzotriazol-2-
yl)-4,6-
ditertpentylphenol
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
sodium
peroxometaborate
2,4-di-tert-butyl-6-(5-
chlorobenzotriazol-2-
yl)p
2-benzotriazol-2-
yl-4,6-di-tert-
butylphenol
ammoniumpentadecafluorooctanoate
disodium 4-
amino-3-[[4'-[(2,4-
diaminophenyl)azo]
1,3-propanesultone
1-vinylimidazole
1,2-diethoxyethane
disodium 3,3'-[[1,1'-
biphenyl]-4,4'-
diylbis(azo)
dodecamethylcyclohexasiloxane
perfluorooctanoic acid

	di-n-pentyl phthalate (DPP)
	furan
	4-o-tolylazo-o-toluidine
	ethylene thiourea
	4-methyl-m-phenylenediamine
	o-toluidine
	butyl 4-hydroxybenzoate
	phenanthrene
	dicyclohexyl phthalate
	p-(1,1-dimethylpropyl)phenol
	N-methylacetamide
	dimethyl sulphate
	pentacosafuorotridecanoic acid
	Perfluorohexane-1-sulphonic acid and its salts
	5-sec-butyl-2-(2,4-dimethylcyclohex-3-en-1-yl)-5
	1,2-benzenedicarboxylic acid, di-C6-10-alkyl est
	reaction mass of 2-ethylhexyl 10-ethyl-4,4-dioct
	Cadmium sulphate
	Bisphenol-A
	Methylhexahydrophthalic anhydride
	Perfluorononan-1-oic acid
	(2,2,3,3,4,4,5,5,6,6,7
	Reaction
	products of 1,3,4-thiadiazolidine-2,5-d
	Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
	Pyrene
	Perfluorobutane
	sulfonic acid (PFBS) and its sal
	Tris(4-nonylphenyl, branched and linear)
	phosphi
	Nonadecafluorodecanoic acid (PFDA) and its sodiu
	4-Nonylphenol, branched and linear, ethoxylated
	Trixylyl phosphate
	4-Nonylphenol, branched and linear
	[substances w
	Zirconia
	Aluminosilicate
	Refractory Ceramic
	Fibr

Aluminosilicate
Refractory Ceramic
Fibres
Sodium dichromate
4,4'-Oxydianiline and
its salts
Boric acid
Disodium tetraborate
n-pentyl-
isopentylphthalate
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
2-benzyl-2-
dimethylamino-4-
morpholinobutyropheno
2-methyl-1-(4-
methylthiophenyl)-2-
morpholinoprop
1,2-
benzenedicarboxylic
acid, dipentylester,
bra
benzo[a]pyrene
1,2-
benzenedicarboxylic
acid; di-C6-8-
branched a
1,2,3-trichloropropane
N-methyl-2-
pyrrolidone
1,2-
benzenedicarboxylic
acid; di-C7-11-
branched
2-ethoxyethyl acetate
cobalt sulphate
cobalt dinitrate
cobalt carbonate
2-methoxyethanol
2-ethoxyethanol
trichloroethylene
tetraboron disodium
heptaoxide, hydrate
potassium dichromate
potassium chromate
Pitch, coal tar, high-
temp.; Pitch
Lead chromate
molybdate sulfate red
lead chromate
Anthracene oil,
anthracene-low;
Anthracene Oil F
lead hydrogen
arsenate
bis(tributyltin) oxide
alkanes, C10-13,
chloro
bis(2-ethylhexyl)
phthalate (DEHP)
musk xylene
diarsenic trioxide
diarsenic pentaoxide
cobalt dichloride

dibutyl phthalate (DBP)
4,4'-diaminodiphenylmethane
potassium hydroxyoctaoxodizincatedichromate(1-)
Fatty acids, C16-18, lead salts
[phthalato(2-)]dioxotrilead
Silicic acid (H2Si2O5), barium salt (1:1), lead-
Sulfurous acid, lead salt, dibasic
lead
bis(tetrafluoroborate) dioxobis(stearato)trilead
tetralead trioxide
sulphate
lead titanium trioxide
lead oxide sulfate
Silicic acid, lead salt
lead dinitrate
cadmium
lead
[4-[[4-anilino-1-naphthyl][4-(dimethylamino)phen
1,3,5-tris(oxiranylmethyl)-1,3,5-triazine-2,4,6(
Lead oxide
trilead bis(carbonate) dihydroxide
orange lead
cadmium oxide (non-pyrophoric)
diboron trioxide
cadmium carbonate
N,N,N',N'-tetramethyl-4,4'-methylenedianiline
2,2'-dichloro-4,4'-methylenedianiline
dichromium
tris(chromate)
bis(2-methoxyethyl) phthalate
pentazinc chromate
octahydroxide
trilead diarsenate
arsenic acid

Halogen-Free Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[216270 Series](#)

This document was generated on 10/15/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION