


Technical Specifications



ITEM	E2	
CONSTRUCTION	Build Volume (W×D×H)	
	Single Extruder Print	Dual Extruder Print
	13×9.4×9.4 inch / 330×240×240 mm	11.6×9.4×9.4 inch / 295×240×240 mm
	Machine Size (W×D×H)	
	23.9×23.5×18.3 inch / 607×596×465 mm	
ELECTRICAL	Power Supply Input	100-240 V AC, 50/60 Hz 230 V @ 2 A
	Power Supply Output	24 V DC, 350 W
PRINTER	Print Technology	FFF
	Print Head System	Independent Dual Extruders
	Filament Diameter	1.75 mm
	XYZ Step Size	0.78125, 0.78125, 0.078125 micron
	Print Head Travel Speed	30 - 150 mm/s
	Build Plate	Flexible Steel Plate with Buildtak
	Max Build Plate Temperature	110 °C
	Heated Bed Material	Silicone
	Build Plate Leveling	Mesh-leveling with Flatness Detection
	Supported Materials	PLA/ ABS/ HIPS/ PC/ TPU/ TPE/ NYLON/ PETG/ ASA/ PP/ PVA/ Glass Fiber Infused/ Carbon Fiber Infused/ Metal Fill/ Wood Fill
	Layer Height	0.02 - 0.25 mm
	Nozzle Diameter	0.4 mm (Default), 0.2/ 0.6/ 0.8/ 1.0 mm (Available)
	Hot End	V3P (V3 hotend with PTFE version)
	Max Nozzle Temperature	300 °C
	Connectivity	Wi-Fi, LAN, USB port, Live camera
	Noise Emission (Acoustic)	< 50 dB(A) when building
	Operating Ambient Temperature	15 - 30 °C, 10 - 90% RH non-condensing
	Storage Temperature	-25 to 55 °C, 10 - 90% RH non-condensing
	Technical Certifications	CB, CE, FCC, RoHS, RCM
	Filter	HEPA filter with activated charcoal
SOFTWARE	Slicing Software	ideaMaker
	Supported File Types	STL/ OBJ/ 3MF
	Supported OS	Windows/ macOS/ Linux
	Machine Code Type	GCODE
PRINTER CONTROLLER	User Interface	7-inch Touch Screen
	Network	Wi-Fi, Ethernet
	Resume Print after Power Outage	Firmware recording, no need for battery installation.
	Screen Resolution	1024×600
	Motion Controller	Atmel ARM Cortex-M4 120MHz FPU
	Logic Controller	NXP ARM Cortex-A9 Quad 1 GHz
	Memory	1 GB
	Onboard Flash	8 GB
	OS	Embedded Linux
	Ports	USB 2.0×2, Ethernet×1