V10PM63

Vishay General Semiconductor


High Current Density Surface-Mount TMBS[®] (Trench MOS Barrier Schottky) Rectifier

Ultra Low $V_F = 0.42$ V at $I_F = 5$ A

eSMP[®] Series

www.vishay.com





LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS				
I _{F(AV)}	10.0 A			
V _{RRM}	60 V			
I _{FSM}	180 A			
V _F at I _F = 10.0 A (T _J = 125 °C)	0.52 V			
T _J max.	175 °C			
Package	SMPC (TO-277A)			
Circuit configuration	Single			

FEATURES

- Very low profile typical height of 1.1 mm
- Trench MOS Schottky technology
- Low forward voltage drop, low power losses
- High efficiency operation
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 Automotive ordering code; base P/NHM3
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

MECHANICAL DATA

Case: SMPC (TO-277A)

Molding compound meets UL 94 V-0 flammability rating

Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Base P/NHM3 - halogen-free, RoHS-compliant, and AEC-Q101 qualified

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 and HM3 suffix meets JESD 201 class 2 whisker test

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)				
PARAMETER	SYMBOL	V10PM63	UNIT	
Device marking code		10M63		
Maximum repetitive peak reverse voltage	V _{RRM}	60	V	
Maximum average forward rectified current (fig. 1)	I _F ⁽¹⁾	10.0	— A	
	I _F ⁽²⁾	4.5		
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	I _{FSM}	180	A	
Operating junction temperature range	T _J ⁽³⁾	-40 to +175	°C	
Storage temperature range	T _{STG}	-55 to +175	°C	

Notes

⁽¹⁾ Mounted on 30 mm x 30 mm pad areas aluminum PCB

⁽²⁾ Free air, mounted on recommended copper pad area

 $^{(3)}$ The heat generated must be less than the thermal conductivity from junction-to-ambient: dP_D/dT_J <1/ R_{θ JA}

Revision: 24-Jun-2020

1

Document Number: 87026

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>





www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT
Instantaneous forward voltage	I _F = 5.0 A	T 25 °C	V _F ⁽¹⁾	0.52	-	v
	I _F = 10.0 A			0.58	0.65	
	I _F = 5.0 A	T _J = 125 °C		0.42	-	
	I _F = 10.0 A			0.52	0.57	
Reverse current	V 60.V	T _J = 25 °C T _J = 125 °C	I _R ⁽²⁾	-	0.025	- mA
	V _R = 60 V			1.6	5.0	
Typical junction capacitance	4.0 V, 1 MHz		CJ	2060	-	pF

Notes

SHAY

 $^{(1)}\,$ Pulse test: 300 μs pulse width, 1 % duty cycle

⁽²⁾ Pulse test: pulse width \leq 5 ms

THERMAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted)				
PARAMETER	SYMBOL	V10PM63	UNIT	
Typical thermal resistance	R _{0JA} (1)(2)	75	°C/W	
	R _{0JM} ⁽³⁾	4		

Notes

 $^{(1)}$ The heat generated must be less than the thermal conductivity from junction to ambient: $dP_D/dT_J < 1/R_{\theta JA}$

⁽²⁾ Free air mounted on recommended copper pad area; thermal resistance $R_{\theta JA}$ - junction to ambient ⁽³⁾ Mounted on 30 mm x 30 mm aluminum PCB; thermal resistance $R_{\theta JM}$ - junction to mount

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
V10PM63-M3/H	0.10	Н	1500	7" diameter plastic tape and reel	
V10PM63-M3/I	0.10	I	6500	13" diameter plastic tape and reel	
V10PM63HM3/H ⁽¹⁾	0.10	Н	1500	7" diameter plastic tape and reel	
V10PM63HM3/I ⁽¹⁾	0.10		6500	13" diameter plastic tape and reel	


Note

(1) AEC-Q101 qualified



Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25$ °C unless otherwise noted)






Fig. 2 - Forward Power Loss Characteristics




Fig. 3 - Typical Instantaneous Forward Characteristics





Fig. 4 - Typical Reverse Leakage Characteristics Per Diode






Fig. 6 - Typical Transient Thermal Impedance

Revision: 24-Jun-2020


3

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

Vishay General Semiconductor

Www.vishay.com

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.