

# HUBER+SUHNER® DATA SHEET

## Coaxial PCB Connector: 90\_MMCX-S50-0-55/119\_O

Rev.: C



### Description

Straight PCB jack

Interface standards  
SUHNER-MMCX



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 6 GHz

#### Mechanical Data

Board mounting type surface mount  
Weight 0.0002 kg

#### Environmental Data

Operating Temperature -40 °C to 90 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts

Centre contact  
Outer contact  
Body  
Insulator

##### Material

Bronze  
Brass  
LCP

##### Surface Plating

Gold Plating (without Nickel underplating)  
Gold Plating (without Nickel underplating)

### Related Documents

Outline drawing DOU-00080379  
Mounting hole DOU-00012840

### Ordering Information

Single package 90\_MMCX-S50-0-55/119\_OE  
Bulk 100 pcs package 90\_MMCX-S50-0-55/119\_OH

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**