


Request Samples (>)



Check Inventory (>)





FEATURES

- Shielded construction
- Soft saturation
- Low DCR per cubic mm
- Designed for switching frequencies between 100KHz-5MHz
- Automotive option available upon request





ELECTRICAL SPECIFICATIONS @ 25°C

PART NUMBER*	INDUCTANCE	TOLERANCE (%)	IRMS (A)	ISAT (A)	DC RESISTANCE (mΩ)		TYPE	
	(uH)	(70)			TYP	MAX		
AMDLA3010S-R15MT	0.15	20	8.0	12	9.3	12	Lead Frame	
AMDLA3010S-R22MT	0.22	20	7.0	11	11	14	Lead Frame	
AMDLA3010S-R33MT	0.33	20	6.0	10	15	18	Lead Frame	
AMDLA3010S-R47MT	0.47	20	4.0	7.0	22	25	Lead Frame	
AMDLA3010S-1R0MT	1.0	20	2.8	5.0	40	48	Lead Frame	
AMDLA3010S-1R5MT	1.5	20	2.4	4.0	54	65	Lead Frame	
AMDLA3010S-2R2MT	2.2	20	1.8	3.5	87	100	Lead Frame	
AMDLA3010S-100MT	10.0	20	0.9	1.4	380	430	Lead Frame	

^{*} Please refer to Part Identification section

Test Conditions

Inductance: 1 MHz, 1 V, 0 Adc Humidity Range: 65% RH

Temperature Rise Current: Current measured at Δ T of 40°C Saturation Current: Current measured at Δ L of 30%

GENERAL SPECIFICATIONS

Operating Temperature:

-55°C to +125°C with (40°C rise) Irms current.

Maximum Part Temperature: +125°C **Components Storage Temperature:**

-55°C to +125°C

Tape and Reel Packaging Temperature: -20°C to +65°C

MSL: Level 1

MATERIALS

Metal Alloy Core: Wire: Copper Terminal: Tin Plating Black Ink:

PART BUILDER




1. Tolerance: M = 20%


2. Packaging: B = Bulk

T = Tape and Reel (4,000pcs/reel)

PRODUCT DIMENSIONS



RECOMMENDED LANDING PATTERN






^{*}Refer to Electrical Specification table



RECOMMENDED REFLOW PROFILE



ZONE	DESCRIPTION	TEMPERATURE	TIMES		
1	Preheat	T _{smin} ~ T _{smax} 150°C ~ 180°C	60 ~ 120 sec.		
2	Reflow	T _∟ 230°C	30 ~ 40 sec.		
3	Peak Heat	T _P 250°C+0/-5°C	10 sec. MAX		






PACKAGING


Tape and Reel: 4,000 Units per Carton: 32,000

T&R per Carton: 8


Weight per Carton: 12.0 kg Weight per Unit: 0.32 g

Carton Dimensions: 360 x 360 x 400 mm





TYPE	А	В	С	D
13" x 12 mm	12.4 +2/-0	100.0 ± 0.5	13.0 +0.5/-0.2	330.0



B _o	A_{o}	K _o	Р	W	F	T	D
3.8 ± 0.1	3.4 ± 0.1	1.5 ± 0.1	8.0 ± 0.1	12.0 ± 0.3	5.5 ± 0.1	0.3 ± 0.05	1.5

Dimensions: mm

This product is commercial off-the-shelf (COTS) and not specifically designed for automotive, military, aviation, aerospace, implantable, life-dependent medical or safety applications. This product is not recommended for use in any application requiring high reliability in which component failure could result in loss of life and/or property damage without prior written approval from Abracon. Specifications are subject to change without notice. Contact Abracon for more information.



Headquarters:

5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858